

[See all 10 Products in Family](#)

**TECHSPEC® 25.0mm Diameter x 125.0mm FL, 980nm V-Coat, PCX Lens**



633nm Laser Line Coated Plano-Convex(PCX) Lenses

Stock **#69-571** CLEARANCE **1 In Stock**

[Other Coating Options](#)

1  MRP ₹2,397

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹2,397 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Plano-Convex Lens Type:

**Physical & Mechanical Properties**

25.00 +0.0/-0.025 Diameter (mm):

<1 Centering (arcmin):

Center Thickness CT (mm):  
3.50 ±0.10

Edge Thickness ET (mm):  
2.28

Clear Aperture CA (mm):  
24

Bevel:  
Protective as needed

## Optical Properties

Effective Focal Length EFL (mm):  
125.00 @ 587.6nm

Back Focal Length BFL (mm):  
122.70

Coating:  
Laser V-Coat (980nm)

Coating Specification:  
 $R_{\text{abs}} < 0.25\%$  @ 980nm

Substrate:   
**N-BK7**

Surface Quality:  
40-20

Power (P-V) @ 632.8nm:  
1.5λ

Irregularity (P-V) @ 632.8nm:  
λ/4

Focal Length Tolerance (%):  
±1

Radius  $R_1$  (mm):  
64.62

f#:  
5.00

Numerical Aperture NA:  
0.10

Design Wavelength DWL (nm):  
980

Damage Threshold, By Design:   
5 J/cm<sup>2</sup> @ 980nm, 10ns

## Regulatory Compliance

Reach 224:  
**Compliant**

Certificate of Conformance:  
**View**

Country of Origin:  
Japan

Imported By:  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- <0.25% Reflection at 980nm
- BBAR Coating Options Also Available: [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), [NIR II](#)
- [405nm](#), [532nm](#), [633nm](#), [785nm](#), 980nm, [1064nm](#), and [1550nm](#) V-Coated Options Offered

Our standard TECHSPEC® Plano-Convex lenses are available in a variety of laser line V-Coat AR coating options. Designed for maximum throughput at the specified laser wavelength, these lenses are ideal for applications utilizing low power HeNe, Diode, and Nd:YAG laser sources. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components.>

## Technical Information



## Compatible Mounts