

TECHSPEC®

25.0mm Dia. x 25.0mm FL, VIS 0° Coated, Plano-Convex Lens



Stock **#47-342** 10 TO 12 DAYS
[Other Coating Options](#)

-

1

+

₹3,785.00

ADD TO CART

Qty 1-9
₹3,785.00
Qty 10+
₹3,415.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):
25.00 @ 587.6nm

Back Focal Length BFL (mm): 20.22
Coating: VS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-SF5
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 8.00 ±0.10
Edge Thickness ET (mm): 2.43
Radius R₁ (mm): 16.82
Clear Aperture CA (mm): 24
f/#: 1
Numerical Aperture NA: 0.50
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View