

[See all 100 Products in Family](#)

TECHSPEC® 25.4 x 272.2mm EFL 30° Protected Aluminum 100Å Off-Axis Parabolic Mirror



TECHSPEC Aluminum Off-Axis Parabolic Mirrors

Stock **#35-606** **3 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ MRP ₹60,434

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹60,434 each
Qty 6-10	₹54,380 each
Qty 11-25	₹51,959 each
Need More?	Request Quote

Product Downloads

General

Off-Axis Parabolic Mirror **Type:**

Physical & Mechanical Properties

136.12 **Y Offset (mm):**

25.40 +0.00/-0.38	Diameter (mm):
90	Clear Aperture (%):
<100 RMS	Surface Roughness (□):
Optical Properties	
Metal	Coating Type:
Protected Aluminum (400-2000nm)	Coating:
30	Off-Set Angle (°):
400 - 2000	Wavelength Range (nm):
272.24	Effective Focal Length EFL (mm):
Aluminum 6061-T6	Substrate: □
R _{avg} ≥85% @400 - 700nm R _{avg} ≥97% @2,000 - 12,000nm	Coating Specification:
±1	Focal Length Tolerance (%):
254.00	Parent Focal Length PFL (mm):
λ/4	Surface Figure, RMS:
80-50	Surface Quality:
508.00	Radius of Curvature (mm):
λ/2	Reflected Wavefront, RMS:

Threading & Mounting	
#47-111	Compatible Mounting Plates:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


Product Details

- Aluminum Coatings for UV, Visible, and NIR Applications
- Range of Surface Roughness, Including 50Å and 100Å
- 15°, 30°, 45°, 60°, or 90° Offset Angle Options
- Gold and Silver Coated Off-Axis Parabolic Mirrors Also Available

TECHSPEC® Aluminum Off-Axis Parabolic Mirrors (OAPs) are a cost-effective solution for focusing incident light with minimal scatter loss. Available with enhanced or protected aluminum coatings, these OAP mirrors offer high reflectivity from the ultraviolet (UV) to the near infrared (NIR). These Aluminum OAPs are manufactured with multiple surface roughness specifications, offering designers the choice between high performance, low scatter mirrors and

more cost sensitive options. TECHSPEC® Aluminum Off-Axis Parabolic Mirrors are used in optical systems such as Schlieren and spectroscopy systems, as well as in laser systems to focus laser beams. For increased system integration flexibility, mounting plates that thread to the base of these off-axis parabolic mirrors are available.

Technical Information



;