


TECHSPEC[®] 25.4 x 25.4mm 343nm 0-45°, Yb:YAG Laser Line Mirror



TECHSPEC[®] Yb:YAG Laser Line Mirrors

Stock #39-607 10 TO 12 DAYS

-

1

+

₹14,964.00

ADD TO CART

Qty 1-5
₹14,964.00
Qty 6+
₹13,485.00
Volume Pricing
Request Quote

Get Product Downloads



Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%) : 85
Back Surface: Commercial Polish
Reflection at DWL (%) : 99.8
Coating Specification: R _{abs} >99.8% @ 343nm
Wavelength Range (nm) : 339 - 346
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (343nm)
Design Wavelength DWL (nm) : 343
Dimensions (mm) : 25.4 x 25.4 +0.00/-0.10
Thickness (mm) : 6.35 ±0.20
Angle of Incidence (°) : 0-45
Substrate: ☐ Fused Silica (Corning 7980)
Damage Threshold, By Design: ☐ 5 J/cm² @ 343nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View