

[See all 44 Products in Family](#)

**TECHSPEC® 25.4 x 25.4mm x -75mm FL, NIR II Imaging Grade PCV Cylinder Lens**



TECHSPEC® Beam Shaping PCV Cylinder Lenses

Stock **#35-019** [CONTACT US](#)

⊖ 1 ⊕ ₹9,264

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹9,264 each
Qty 6-25	₹8,408 each
Qty 26-49	₹7,941 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Cylinder Lens, Plano-Concave **Type:**

**Physical & Mechanical Properties**

Protective as needed **Bevel:**

4.00 **Center Thickness CT (mm):**

±0.1	<b>Center Thickness Tolerance (mm):</b>
22.86 x22.86	<b>Clear Aperture CA (mm):</b>
<hr/>	
+0.0/-0.025	<b>Dimensional Tolerance (mm):</b>
25.4 x25.4	<b>Dimensions (mm):</b>
<hr/>	
6.07	<b>Edge Thickness ET (mm):</b>
<3	<b>Axial Twist (arcmin):</b>

## Optical Properties

-75.00	<b>Effective Focal Length EFL (mm):</b>
<b>N-BK7</b>	<b>Substrate:</b> <input type="checkbox"/>
<hr/>	
3	<b>f#:</b>
0.08	<b>Numerical Aperture NA:</b>
<hr/>	
NIR II (750-1550nm)	<b>Coating:</b>
750 - 1550	<b>Wavelength Range (nm):</b>
<hr/>	
-77.64	<b>Back Focal Length BFL (mm):</b>
R <sub>abs</sub> ≤1.5% @ 750 - 800nm R <sub>abs</sub> ≤1.0% @ 800 - 1550nm R <sub>avg</sub> ≤0.7% @ 750 - 1550nm	<b>Coating Specification:</b>
<hr/>	
38.76	<b>Radius R<sub>1</sub> (mm):</b>
40-20	<b>Surface Quality:</b>
<hr/>	
1.5λ	<b>Power (P-V) @ 632.8nm:</b>
λ/4	<b>Irregularity (P-V) @ 632.8nm:</b>
<hr/>	
<5	<b>Plano Axis Wedge (arcmin):</b>
<5	<b>Power Axis Wedge (arcmin):</b>

## Regulatory Compliance

<b>Compliant</b>	<b>RoHS 2015:</b>
<b>View</b>	<b>Certificate of Conformance:</b>
<hr/>	
<b>Compliant</b>	<b>Reach 235:</b>
<hr/>	
China	<b>Country of Origin:</b>
Edmund Optics India Private Limited	<b>Imported By:</b>

## Product Details

- Beam Shaping Grade Specifications
- Used with [TECHSPEC® Imaging Grade PCX Cylinder Lenses](#) for Circularizing Beams
- Negative Focal Length

TECHSPEC® Imaging Grade PCV Cylinder Lenses are typically used to diverge collimated light in a single axis. These lenses are designed for system integration due to the tightly controlled specifications and generous volume discounts. TECHSPEC Imaging Grade PCV Cylinder Lenses feature tightly controlled wedge and tilt specifications and are ideal for circularizing elliptical beams in combination with our [TECHSPEC Imaging Grade PCX Cylinder Lenses](#).

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries

- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

---