

[See all 2 Products in Family](#)

TECHSPEC® 25.4mm 45°, 2μm Laser Line Mirror



2μm Laser Line Mirrors

Stock **#37-502** [CONTACT US](#)

⊖ 1 ⊕ MRP ₹36,926

📌 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹36,926 each
Need More?	Request Quote

Product Downloads

General

Laser Mirror **Type:**

Physical & Mechanical Properties

<3 **Parallelism (arcmin):**

90 **Clear Aperture (%):**

Compensating Coating **Back Surface:**

25.40 +0.0/-0.1	Diameter (mm):
6.35 ±0.2	Thickness (mm):
Optical Properties	
40-20	Surface Quality:
99.6	Reflection at DWL (%):
99.6	Reflectivity (Rs%):
99.9	Reflectivity (Rp%):
Coating Specification: R _s >99.9% @ 1900 – 2200nm R _p >99.6% @ 1940 – 2100nm	
1900 - 2200	Wavelength Range (nm):
M7 @2000nm	Surface Flatness (P-V):
Dielectric	Coating Type:
Laser Mirror (1900-2200nm)	Coating:
2000	Design Wavelength DWL (nm):
45	Angle of Incidence (°):
Fused Silica (Coming 7980)	Substrate: <input type="checkbox"/>
>10 J/cm ² @ 2000nm, 10ns, 10Hz	Damage Threshold, By Design: <input type="checkbox"/>

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:
Lithuania	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Laser Damage Threshold >10 J/cm² @ 2µm, 10ns, 10Hz
- Designed for Holmium and Thulium Laser Sources
- M7 Surface Accuracy

TECHSPEC® High Performance 2µm Laser Mirrors are designed for use with Holmium (2100nm) and Thulium (1940nm) doped laser systems. These mirrors are ideal for medical, industrial, and metrology application spaces. The 2 micron wavelength regime is useful for surgical procedures as it can target discrete depth levels of tissue beneath the skin's surface. TECHSPEC® High Performance 2µm Laser Mirrors feature guaranteed laser damage thresholds >10 J/cm² and >99% reflectivity at 2 microns.

Note: For more information on 2µm laser source applications, please see the [Characteristics of 2µm Lasers](#).

Compatible Mounts