

12.7mm Dia. 7°, 1030nm Highly-Dispersive Ultrafast Mirror

See More by [UltraFast Innovations \(UFI\)](#)



Stock #12-334 20+ In Stock

-

1

+

₹36,200

ADD TO CART

Volume Pricing	
Qty 1-3	₹36,200 each
Qty 4-7	₹31,919 each
Qty 8+	₹28,415 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Laser Mirror

Type:

Typical Applications:








Yb:doped 1st Harmonic	
HD1310	Model Number:
Physical & Mechanical Properties	
12.70 +0.0/-0.1	Diameter (mm):
6.35 ±0.2	Thickness (mm):
Commercial Polish	Back Surface:
80	Clear Aperture (%):
10 ±5	Wedge Angle (arcmin):
Optical Properties	
1030	Design Wavelength DWL (nm):
1010 - 1070	Wavelength Range (nm):
7	Angle of Incidence (°):
99.9 (typical, s-polarization)	Reflection at DWL (%):
Fused Silica (Corning 7980)	Substrate: ☐
Dielectric	Coating Type:
R _{avg} >99.8%, GDD = -1000fs ² @ 1010 - 1070nm (s-polarization) R _{abs} >99.9% @ 1030nm (typical, s-polarization)	Coating Specification:
-1000fs ² @ 1010 - 1070nm	GDD Specification:
Ultrafast (1010-1070nm)	Coating:
λ/10	Irregularity (P-V) @ 632.8nm:
>99.8% @ 1010 - 1070nm (s-polarization)	Minimum Reflectivity:
0.3 J/cm ² @ 1030nm, 50fs, 1kHz, 100μm Beam Diameter	Damage Threshold, By Design: ☐
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:



PRODUCT DETAILS

- Highly Negative GDD up to -1000 fs² at 7° AOI
- >99.8% Minimum Reflection across 60nm Bandwidth
- Ideal for Dispersion Compensation of Yb:doped Fiber Lasers
- Ultrafast Chirped Coating

UltraFast Innovations (UFI) 1030nm Highly-Dispersive Ultrafast Mirrors are characterized by an exceptionally low GDD and high reflectance over their 60nm bandwidth due to an optimized multilayer coating. Based on dispersive optical interference, the ultrafast chirped coating provides these mirrors with a highly negative GDD of -500fs² or -1000fs² at their design angle of incidence, 5 or 7°. These mirrors feature a typical reflectance of >99.9% at their design wavelength and a minimum reflectance of 99.8% across their bandwidth. UFI 1030nm Highly-Dispersive Ultrafast Mirrors are ideal for pulse compression and dispersion compensation of Yb:doped lasers such as hybrid Mamyshhev fiber and thin disk lasers. Standard imperial sizes of ½" or 1" (12.7mm or 25.4mm) are available; please contact us if your laser system requires a custom size, wavelength, or ultrashort pulses and we would be happy to find the right solution for your application.

TECHNICAL INFORMATION





CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

COMPATIBLE MOUNTS