

[See all 126 Products in Family](#)

## 25.4mm Dia. 1030nm $\lambda$ /4 Quartz Waveplate Zero Order



Stock **#16-888** 1 In Stock

-

1

+

₹38,769

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹38,769 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Type:

Crystalline Waveplate

Configuration:

Air Spaced

Physical & Mechanical Properties

Clear Aperture CA (mm):

20.0

Diameter (mm):

25.40 +0.00/-0.25


Thickness (mm):

|                                            |                                                       |
|--------------------------------------------|-------------------------------------------------------|
| 6.00 +0.00/-0.25                           |                                                       |
| Crystalline                                | Construction:                                         |
|                                            |                                                       |
| <3                                         | Parallelism (arcsec):                                 |
| Optical Properties                         |                                                       |
| Laser V-Coat (1030nm)                      | Coating:                                              |
| 1030                                       | Design Wavelength DWL (nm):                           |
|                                            |                                                       |
| Crystal Quartz                             | Substrate: <input type="checkbox"/>                   |
| $\lambda/4$                                | Retardance:                                           |
|                                            |                                                       |
| 20-10                                      | Surface Quality:                                      |
|                                            |                                                       |
| < $\lambda/10$ @ 632.8 nm                  | Transmitted Wavefront, P-V:                           |
|                                            |                                                       |
| $\pm\lambda/300$                           | Retardance Tolerance:                                 |
|                                            |                                                       |
| 0.0001                                     | Temperature Coefficient ( $\lambda^\circ\text{C}$ ):  |
|                                            |                                                       |
| $R_{\text{abs}} < 0.2\%$ @ on each surface | Coating Specification:                                |
| >10 J/cm <sup>2</sup> @ 1064 nm, 10ns      | Damage Threshold, By Design: <input type="checkbox"/> |
|                                            |                                                       |
| 0                                          | Retardance Order:                                     |
|                                            |                                                       |
| Regulatory Compliance                      |                                                       |
|                                            |                                                       |
| Compliant                                  | RoHS 2015:                                            |
|                                            |                                                       |
| View                                       | Certificate of Conformance:                           |
|                                            |                                                       |
| Compliant                                  | Reach 247:                                            |
|                                            |                                                       |
| China                                      | Country of Origin:                                    |
|                                            |                                                       |
| Edmund Optics India Private Limited        | Imported By:                                          |

## Product Details

- Zero Order and Multiple Order Waveplates
- $\lambda/4$  and  $\lambda/2$  Retardance
- Mounted in Black Anodized Aluminum Frame
- [Zero Order Polymer Waveplates](#) Also Available

Quartz Waveplates (Retarders) are available in multiple order and zero order. These waveplates are ideal for a range of applications. Multiple order waveplates are ideal for applications where the wavelength deviates less than  $\pm 1\%$  from the design wavelength of the waveplate. For applications with a greater than  $\pm 1\%$  deviation, zero order waveplates are recommended due to their increased bandwidth and lower sensitivity to temperature change. Quartz Waveplates (Retarders) have the fast axis marked on the edge of the mount to ease system integration.



## Technical Information

