

[See all 1 Products in Family](#)

25.4mm Dia., 1030nm Highly-Dispersive Ultrafast Mirror with Reduced Thermal Lensing

See More by [UltraFast Innovations \(UFI\)](#)



UltraFast Innovations (UFI) 1030nm Highly-Dispersive Ultrafast Mirrors with Reduced Thermal Lensing

Stock **#17-070** **5 In Stock**

MRP ₹1,12,997

1 Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1-9	₹1,12,997 each
Qty 10+	₹1,02,404 each
Need More?	Request Quote

Product Downloads

General

HD64 **Model Number:**

Physical & Mechanical Properties

10 **Wedge Angle (arcmin):**

80 **Clear Aperture (%):**

Commercial Polish	Back Surface:
25.40 +0.00/-0.05	Diameter (mm):
6.35 ±0.20	Thickness (mm):

Optical Properties

Coating Specification:	
R _{avg} >99.5% @ 1010 - 1050nm (5° AOI, p-polarization)	
GDD Specification:	
-1000fs ² @ 1010 - 1050nm (5° AOI, p-polarization)	
1010 - 1050	Wavelength Range (nm):
λ/10	Irregularity (P-V) @ 632.8nm:
Coating Type:	
Dielectric	
Coating:	
Highly Dispersive (1010-1050nm)	
1030	Design Wavelength DWL (nm):
5	Angle of Incidence (°):
Substrate: <input type="checkbox"/>	
Fused Silica (Corning 7980)	
Damage Threshold, Reference: <input type="checkbox"/>	
>0.3 J/cm ² for 1 ps @ 5 kHz rep rate @ 1030nm	

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:
Germany	Country of Origin:
Imported By:	
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Ultrafast Highly-Dispersive Coating with Reduced Thermal Lensing
- Highly Negative GDD up to -1000 fs² at 5° AOI
- >99.5% Minimum Reflection (P-Polarization) across 50nm Bandwidth
- Ideal for the Generation of High-Power Ultrafast Laser Pulses

UltraFast Innovations (UFI) 1030nm Highly-Dispersive Ultrafast Mirrors with Reduced Thermal Lensing provide a GDD of -1000fs² and low loss with negligible thermal effects. Thermal lensing can occur if an active gain medium is hotter along the beam axis than the rest of the medium, resulting in a transverse refractive index gradient. This can misalign the laser cavity and lead to different laser mode profiles and drifts in beam pointing. These mirrors are designed to provide a high degree of control over beam stability and feature reflectance >99.5% (P-polarization) between 1010 - 1050nm. At a design angle of incidence (AOI) of 5°, these mirrors maximize the number of reflections between a pair of ultrafast mirrors and allow for pulse compression while limiting thermal lensing. UltraFast Innovations (UFI) 1030nm Highly-Dispersive Ultrafast Mirrors with Reduced Thermal Lensing are ideal for intra-cavity applications, ultrafast high energy oscillators, and amplifiers such as Yb:YAG thin-disk laser systems. Please contact us if your laser system requires a custom size, wavelength, or pulse profile.