

[See all 18 Products in Family](#)

## 25.4mm Dia., 2 Arcsec, Low Profile Bare Gold Replicated Hollow Metal Retroreflector



Replicated Hollow Metal Retroreflectors

Stock #23-856 **20+ In Stock**

1 MRP ₹79,703

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-9	₹79,703 each
Qty 10-24	₹74,124 each
Qty 25+	₹67,747 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Retroreflector **Type:**

Low Profile **Style:**

#### Physical & Mechanical Properties

Clear Aperture CA (mm):

22.86

Diameter (mm):

25.40

Height (mm):

20.32

Dimensional Tolerance (mm):

+0.025/-0.051

### Optical Properties

Beam Deviation (arcsec):

2

Coating:

Bare Gold

Substrate: □

Aluminum

Surface Quality:

60-40

Image Orientation:

Left-Handed

Coating Specification:

R<sub>avg</sub> >94% @ 700 - 800nm  
R<sub>avg</sub> >97% @ 800 - 2000nm  
R<sub>avg</sub> >98% @ 2 - 12μm

Ray Deviation (°):

180

Wavelength Range (nm):

700 - 12000

### Threading & Mounting

Mounting Threads:

M2 x 0.4

### Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

United States

Imported By:


Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000


## Product Details

- Monolithic Aluminum Construction
- Return Beam Accuracy Unaffected by Vibration
- Bare Gold or Enhanced Aluminum Coating Options
- Low Profile Versions are Available

Replicated Hollow Metal Retroreflectors feature a monolithic aluminum construction and an integrated mount to provide return beam performance unaffected by vibration. These retroreflectors are offered with bare gold coatings applied to the first surface, maximizing their reflectivity in the infrared (IR), or enhanced aluminum coatings for optimal performance in the visible spectrum. Designed to have the entirety of their optical path in air, these retroreflectors do not require antireflection coatings for optimal performance and can be used over wider wavelength ranges than glass retroreflectors. Replicated Hollow Metal Retroreflectors are ideal for applications where an optical path through a glass prism is undesired, reduced weight is required, or where high shock and vibration levels are expected. The replication manufacturing process of these optics enables cost-effective designs while providing high performance beam return accuracy.

## Technical Information





REPLICATED HOLLOW METAL RETROREFLECTORS					
Diameter (mm)	Height (mm)	Mounting Threads	Coating	Stock No.	
				5 Arcseconds	10 Arcseconds
12.7	21.68	10-24	Bare Gold	<a href="#">#15-897</a>	<a href="#">#15-898</a>
19.1	26.17	10-24	Bare Gold	<a href="#">#15-899</a>	<a href="#">#15-900</a>
25.4	30.66	10-24	Bare Gold	<a href="#">#15-901</a>	<a href="#">#15-902</a>
38.1	39.64	10-24	Bare Gold	<a href="#">#15-903</a>	<a href="#">#15-904</a>

Diameter

Height

10-24 Mounting Threads

LOW PROFILE REPLICATED HOLLOW METAL RETROREFLECTORS

Dimension A (mm)	Dimension B (mm)	Dimension C (mm)	Coating	Stock No.		
				2 Arcseconds	5 Arcseconds	10 Arcseconds
12.7	8.63	12.8	Bare Gold	N/A	#23-854	#23-855
25.4	21.69	20.32	Bare Gold	#23-856	#23-857	#23-858

