

TECHSPEC® 25.4mm Dia., 6.35mm Thick, 343nm,  $\lambda/10$  Fused Silica Window



TECHSPEC  $\lambda/10$  Laser Line Coated Windows

Stock **#39-671** [CONTACT US](#)

-

1

+

₹11,589

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | ₹11,589 each                  |
| Qty 6-25       | ₹9,242 each                   |
| Qty 26-49      | ₹8,729 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                 |
|----------------------------------|-----------------|
| Laser Line Window                | Type:           |
| Glass                            | Type of Window: |
| Physical & Mechanical Properties |                 |
| 6.35 ±0.20                       | Thickness (mm): |

|                      |                         |
|----------------------|-------------------------|
| 22.86                | Clear Aperture CA (mm): |
| 25.40 +0.00/-0.10    | Diameter (mm):          |
| 90                   | Clear Aperture (%):     |
| <3                   | Parallelism (arcmin):   |
| Protective as needed | Bevel:                  |
| Fine Ground          | Edges:                  |

|                                           |                                                       |
|-------------------------------------------|-------------------------------------------------------|
| Optical Properties                        |                                                       |
| Fused Silica (Corning 7980)               | Substrate: <input type="checkbox"/>                   |
| 1.458                                     | Index of Refraction (n <sub>d</sub> ):                |
| 10-5                                      | Surface Quality:                                      |
| 0                                         | Angle of Incidence (°):                               |
| Laser V-Coat (343nm)                      | Coating:                                              |
| 343                                       | Design Wavelength DWL (nm):                           |
| 67.8                                      | Abbe Number (v <sub>d</sub> ):                        |
| λ/10                                      | Surface Flatness (P-V):                               |
| R <sub>abs</sub> <0.25% @ 343nm           | Coating Specification:                                |
| 7.5 J/cm <sup>2</sup> @ 343nm, 20ns, 20Hz | Damage Threshold, By Design: <input type="checkbox"/> |
| 7.5 J/cm <sup>2</sup> @ 343nm, 20ns, 20Hz | Damage Threshold, Pulsed:                             |

|                     |                     |
|---------------------|---------------------|
| Material Properties |                     |
| 7980 0F             | Fused Silica Grade: |




|                                     |                             |
|-------------------------------------|-----------------------------|
| Regulatory Compliance               |                             |
| Compliant                           | RoHS 2015:                  |
| Compliant                           | Reach 209:                  |
| View                                | Certificate of Conformance: |
| Singapore                           | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |

## Product Details

- 10-5 Surface Quality
- Damage Thresholds at Design Wavelengths
- Diameters from 12.5 to 76.2mm Available
- Uncoated Substrates Available

TECHSPEC® λ/10 Laser Line Coated Windows are designed for direct integration into laser applications. This robust product family features common imperial sizes, many of which offer multiple thickness options. Anti-reflection coatings are available at common laser wavelengths, minimizing surface reflection for optimal system transmission. TECHSPEC λ/10 Laser Line Coated Windows provide laser grade specifications including λ/10 surface flatness, 10-5 surface quality, and <3 arcmin parallelism. These windows are ideal for industrial laser applications ranging from protective coverings to separating various environments.

## Technical Information



## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Compatible Mounts