

[See all 3 Products in Family](#)

25.4mm Dia., 3mm Thick, 3° Wedge, ISP Optics Calcium Fluoride (CaF₂) Wedged Window | CF-WW3-25-3

See More by [ISP Optics](#)



Calcium Fluoride (CaF₂) Wedged Windows

Stock **#19-719** **7 In Stock**

MRP ₹27,544

1 Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹27,544 each
Need More?	Request Quote

Product Downloads

General

CF-WW3-25-3 **Model Number:**

Protective Window **Type:**

Crystal **Type of Window:**

Physical & Mechanical Properties

21.59 **Clear Aperture CA (mm):**

25.40 +0.00/-0.13 **Diameter (mm):**

3.00 ±0.13 **Thickness (mm):**

Protective as needed **Bevel:**

85 **Clear Aperture (%):**

Fine Ground **Edges:**

0.26 **Poisson's Ratio:**

75.8 **Young's Modulus (GPa):**

158.30 **Knoop Hardness (kg/mm²):**

Optical Properties

Uncoated **Coating:**

[Calcium Fluoride \(CaF₂\)](#) **Substrate:**

1.495 **Index of Refraction (n_d):**

60-40 **Surface Quality:**

200 - 7000 **Wavelength Range (nm):**

2λ@633nm **Surface Flatness (P-V):**

3° ±0.25 **Wedge Angle (°):**

Material Properties

3.18 **Density (g/cm³):**

18.85 **Coefficient of Thermal Expansion CTE (10⁻⁶/°C):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 240:**

Latvia **Country of Origin:**

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000 **Imported By:**

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).


Product Details

- 30 Arcmin Wedge
- Low Absorption, High Transmission

- Ideal for Harsh Environments
- [Precision Flat Calcium Fluoride Windows](#) Also Available

ISP Optics Calcium Fluoride (CaF₂) Wedged Windows feature a 30 arcmin wedge to eliminate fringe patterns from etalon effects and to prevent cavity feedback. Calcium fluoride's combination of low absorption and high damage threshold make these windows a popular choice for free-space lasers. Its low refractive index allows it to be used without an anti-reflective coating. ISP Optics Calcium Fluoride (CaF₂) Wedged Windows feature low water solubility and offer superior hardness compared to other fluoride-based substrates, making them suitable for laser applications in harsh environments. Calcium Fluoride (CaF₂) Wedged Windows provide laser output protection from environmental effects and are ideal for beam sampling applications.

Technical Information



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools