


TECHSPEC®

100 x 100mm λ /10 ZERODUR® Uncoated Mirror Substrate



Stock **#71-525** **1 In Stock**

-

1

+

₹32,386

ADD TO CART

Volume Pricing	
Qty 1+	₹32,386 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Mirror Substrate

Type:

Physical & Mechanical Properties

10.00 ±0.20

Thickness (mm):

100.0 x 100.0 +0.00/-0.20	Dimensions (mm):
Commercial Polish	Back Surface:
Protective as needed	Bevel:
90	Clear Aperture (%):
Ground	Edges:
100.00	Length (mm):
100.00	Width (mm):
30	Parallelism (arcsec):
Optical Properties	
Uncoated	Coating:
$\lambda/10$	Surface Flatness (P-V):
ZERODUR®	Substrate:
20-10	Surface Quality:
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Precision ZERODUR® Substrates
- $\lambda/10$ Flatness
- Low Coefficient of Thermal Expansion

TECHSPEC® ZERODUR Mirror Substrates are well suited for applications where temperature fluctuation is a concern. The ZERODUR® substrates have a coefficient of thermal expansion (CTE) of $\pm 0.10 \times 10^{-6}/^{\circ}\text{C}$, which is an order of magnitude lower than most glass types. The low CTE allows these mirrors to have a consistent reflected wavefront, even when exposed to environments with varying temperature or illumination sources with changing intensity. TECHSPEC® ZERODUR Mirror Substrates feature precision polished substrates with $\lambda/10$ flatness and 20-10 surface quality.