

[See all 3 Products in Family](#)

TECHSPEC® 25.4mm Dia., 6.35mm Thick, 355nm, Nd:YAG IBS Laser Line Window



TECHSPEC® IBS Laser Line Windows

Stock **#12-969** **20+ In Stock**

MRP ₹17,757

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹17,757 each
Qty 6-25	₹14,226 each
Qty 26-49	₹13,317 each
Need More?	Request Quote

Product Downloads

General

Laser Line Window **Type:**

Glass **Type of Window:**

Physical & Mechanical Properties

Clear Aperture CA (mm):

22.86	Diameter (mm):
25.40 +0.00/-0.10	
	Thickness (mm):
6.35 ±0.20	
	Parallelism (arcmin):
<3	
	Bevel:
Protective as needed	
	Clear Aperture (%):
90	
	Edges:
Fine Ground	
	Poisson's Ratio:
0.16	
	Young's Modulus (GPa):
73	
	Knoop Hardness (kg/mm²):
522.00	

Optical Properties

	Angle of Incidence (°):
0	
	Coating:
Laser Ultra V-Coat, IBS (355nm)	
	Design Wavelength DWL (nm):
355	
	Substrate: <input type="checkbox"/>
Fused Silica (Corning 7980)	
	Index of Refraction (n_d):
1.458	
	Surface Quality:
10-5	
	Abbe Number (v_d):
67.8	
	Coating Specification:
R _{abs} <0.10% @ 355nm	
	Surface Flatness (P-V):
λ/10	
	Damage Threshold, Certified: <input type="checkbox"/>
7.5 J/cm ² @ 355nm, 20ns, 20Hz	

Material Properties

	Density (g/cm³):
2.20	
	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
0.52 (+5 to +35°C)	
0.57 (0 to +200°C)	
0.48 (-100 to +200°C)	
	Fused Silica Grade:
7980 0F	

Regulatory Compliance

	Certificate of Conformance:
View	
	Country of Origin:
Lithuania	
	Imported By:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:


- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- IBS Coated for Minimal Absorption and Scatter
- <0.1% Reflectivity at Nd:YAG Laser Lines
- Certified Laser Damage Thresholds at Design Wavelength

TECHSPEC® IBS Laser Line Windows feature an ion beam sputtering (IBS) anti-reflection coating that provides <0.1% reflectivity at their design wavelength with minimal losses due to absorption or scatter. The IBS coating process produces dense, homogeneous coating layers that are environmentally stable and insensitive to temperature and humidity changes, enabling these windows to be used in harsh environments. TECHSPEC IBS Laser Line Windows are available in standard imperial sizes with designs for the Nd:YAG laser wavelengths of 355nm, 532nm, and 1064nm. In-house manufacturing enables Edmund Optics to provide custom sizes and designs in the wavelength range 343nm to 1600nm.



Superpolished Optics for Minimized Scatter

LEARN
MORE [▶](#)

Compatible Mounts
