


25.4mm Dia., 1mm Thick, 3-5µm BBAR Coated, ISP Optics Silicon (Si) Window | HDAR35-SI-W-25-1

See More by [ISP Optics](#)



Stock **#24-638** CLEARANCE **12 In Stock**

-

1

+

₹9,716

ADD TO CART

Volume Pricing	
Qty 1+	₹9,716 each
Need More?	Request Quote

Product Downloads

General	
Model Number:	HDAR35-SI-W-25-1
Type:	Protective Window

Physical & Mechanical Properties	
Clear Aperture CA (mm):	21.59

25.40 +0.00/-0.13	Diameter (mm):
1.00 ±0.13	Thickness (mm):
<3	Parallelism (arcmin):
Protective as needed	Bevel:
85	Clear Aperture (%):
Fine Ground	Edges:
0.27	Poisson's Ratio:
140	Young's Modulus (GPa):
1,150.00	Knoop Hardness (kg/mm²):

Optical Properties

BBAR (3000-5000nm)	Coating:
Silicon (Si)	Substrate: □
3.422 @ 5µm	Index of Refraction (n _d):
40-20	Surface Quality:
R_{avg} <0.5% @ 3 - 5µm R_{abs} <1.5% @ 3 - 5µm	Coating Specification:
3000 - 5000	Wavelength Range (nm):
2λ	Surface Flatness (P-V):

Material Properties

2.33	Density (g/cm³):
2.55	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):

Regulatory Compliance

View	Certificate of Conformance:
Latvia	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Transmission from 1.2 - 7µm
- Available Uncoated or HDAR Coated for 3 - 5µm
- Ideal for Weight Sensitive Applications

ISP Optics Silicon (Si) Windows provide transmission in the Near-Infrared (NIR) and Mid-Wave Infrared (MMIR) from 1.2 - 7µm. Silicon features a Knoop Hardness of 1150, making it harder and less brittle than Germanium. A High-Durability Anti-Reflection (HDAR) coating option increases the durability of the substrate while significantly improving transmission from 3 - 5µm, enabling use in harsh environments. ISP Optics Silicon (Si) Windows are ideal for weight-sensitive IR applications due to its low density of 2.329 g/cm³, which is half as dense as Germanium and Zinc Selenide. These windows are ideal for NIR imaging applications and are important for detection of sources radiating at a black body temperature of 700K.