

[See all 37 Products in Family](#)

## 25.4mm Dia f/0.75 VIS Coated, Molded Acrylic Aspheric Lens



Molded Acrylic Aspheric Lenses



Stock **#33-262** **8 In Stock**

-

1

+

₹5,683

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | ₹5,683 each                   |
| Qty 11-49      | ₹4,710 each                   |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General                          |                         |
|----------------------------------|-------------------------|
| Aspheric Lens                    | Type:                   |
| Physical & Mechanical Properties |                         |
| 25.40 ±0.1                       | Diameter (mm):          |
|                                  | Clear Aperture CA (mm): |

|                      |                           |
|----------------------|---------------------------|
| 23.9                 |                           |
| 4.00                 | Edge Thickness ET (mm):   |
| 12.22                | Center Thickness CT (mm): |
| Protective as needed | Bevel:                    |
| 99.57                | Radius R (mm):            |

Optical Properties

|                                      |                                  |
|--------------------------------------|----------------------------------|
| 19.10 @ 632.8nm                      | Effective Focal Length EFL (mm): |
| 0.67                                 | Numerical Aperture NA:           |
| 12.7                                 | Back Focal Length BFL (mm):      |
| PMMA                                 | Substrate: □                     |
| ±1                                   | Focal Length Tolerance (%):      |
| 632.8                                | Aspheric Design Wavelength (nm): |
| BBAR (450-650nm)                     | Coating:                         |
| R <sub>avg</sub> <0.5% @ 450 - 650nm | Coating Specification:           |
| 0.75                                 | f/#:                             |
| 450 - 650                            | Wavelength Range (nm):           |
| Infinite                             | Conjugate Distance:              |

Environmental & Durability Factors

|       |                             |
|-------|-----------------------------|
| 80.00 | Operating Temperature (°C): |
|-------|-----------------------------|

Regulatory Compliance

|                                     |                             |
|-------------------------------------|-----------------------------|
| Compliant                           | RoHS 2015:                  |
| View                                | Certificate of Conformance: |
| Compliant                           | Reach 242:                  |
| United States                       | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |

## Product Details

- Prescription Information Available
- Reduced Spherical Aberration
- Broadband AR Coating Option

Our molded acrylic aspheres are economical solutions for a variety of photonic applications. With available prescription information, these lenses are easily integrated into both benchtop and OEM applications. They are available uncoated and with broadband antireflection coatings. Standard diameter sizes of 0.5" and 1" allow them to be easily mounted using our full line of [lens mounts](#).

## Compatible Mounts