

[See all 1 Products in Family](#)

25.4mm Dia., 255 - 277nm, Negative Dispersion UV Ultrafast Mirrors

See More by [UltraFast Innovations \(UFI\)](#)



UltraFast Innovations (UFI) 255-277nm Negative Dispersion UV Ultrafast Mirrors

Stock **#17-066** **1 In Stock**

MRP ₹1,23,591

1 Price inclusive of all taxes

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-9 | ₹1,23,591 each |
| Qty 10+ | ₹1,10,979 each |
| Need More? | Request Quote |

Product Downloads

General

Model Number:
HD100

Physical & Mechanical Properties

Wedge Angle (arcmin):
10

Clear Aperture (%):
80

| | |
|---|--|
| Commercial Polish | Back Surface: |
| 25.40 +0.00/-0.05 | Diameter (mm): |
| 6.35 ±0.20 | Thickness (mm): |
| Optical Properties | |
| Coating Specification: R _{avg} >80% @ 255 - 277nm (5° AOI, p-polarization) | |
| GDD Specification: -145fs ² @ 255 - 277nm (5° AOI, p-polarization) | |
| 255 - 277 | Wavelength Range (nm): |
| λ10 | Irregularity (P-V) @ 632.8nm: |
| Dielectric | Coating Type: |
| Highly Dispersive UV (255-277nm) | Coating: |
| 266 | Design Wavelength DWL (nm): |
| 5 | Angle of Incidence (°): |
| Fused Silica (Corning 7980) | Substrate: <input type="checkbox"/> |

| | |
|--|------------------------------------|
| Regulatory Compliance | |
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |
| Compliant | Reach 235: |
| Germany | Country of Origin: |
| Imported By: Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000 | |

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Negative GDD of -145 fs²
- Angle of Incidence of 5° between 255 - 277nm
- Ideal for Pulse Compression or Dispersion Compensation of UV Ultrafast Laser Beams
- Unique UV Negative Dispersion Ultrafast Coating

UltraFast Innovations (UFI) 255-277nm Negative Dispersion UV Ultrafast Mirrors feature fused silica substrates with excellent thermal stability and 25.4mm diameter to facilitate integration into UV applications. Based on dispersive optical interference, the ultrafast chirped coating provides these mirrors with a negative GDD of -145 fs². These mirrors are designed to provide a high degree of control over beam stability and feature a reflectance >80% (P-polarization) between 255 - 277nm. At a design angle of incidence (AOI) of 5°, these mirrors maximize the number of reflections between a pair of ultrafast mirrors while maintaining a small footprint. UltraFast Innovations (UFI) 255-277nm Negative Dispersion UV Ultrafast Mirrors allow compressing UV ultrafast laser pulses such as those generated from the 3rd harmonic of Ti:sapphire lasers and 4th harmonic of Yb:doped lasers. Please contact us if your laser system requires a custom size, wavelength, or pulse profile.