

25.4mm Dia., 6.35mm Thick, 261.4nm, λ /10 Fused Silica Window



TECHSPEC λ /10 Laser Line Coated Windows

Stock **#19-737** CLEARANCE 10 TO 12 DAYS

-

1

+

₹12,785.00

ADD TO CART

Qty 1+
₹12,785.00
Volume Pricing
Request Quote

Get Product Downloads



Angle of Incidence (°): 0
Clear Aperture CA (mm): 22.86
Coating: Laser V-Coat (261.4nm)
Design Wavelength DWL (nm): 261.4
Diameter (mm):

25.40 +0.00/-0.10
Substrate: Fused Silica (Corning 7980)
Index of Refraction n_d: 1.458
Surface Quality: 10-5
Thickness (mm): 6.35 ±0.20
Type: Laser Line Window
Parallelism (arcmin): <3
Bevel: Protective as needed
Clear Aperture (%): 90
Abbe Number (v_d): 67.8
Coating Specification: R _{abs} <0.25% @ 261.4nm
Surface Flatness (P-V): λ/10
Damage Threshold, By Design: 3 J/cm² @ 266nm, 20ns, 20Hz
Edges: Fine Ground
Type of Window: Glass

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View