

[See all 3 Products in Family](#)

25.4mm Dia. 300 - 2700nm Broadband Polarizer



Broadband Polarizers

Stock #89-602 **8 In Stock**

1 MRP ₹1,23,086

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹1,23,086 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Physical & Mechanical Properties

19.05 **Clear Aperture CA (mm):**

25.40 **Diameter (mm):**

2.50 ±0.3 **Thickness (mm):**

Dimensional Tolerance (mm):

+0.0/-0.1

Optical Properties**Angle of Incidence (°):**

±40

Extinction Ratio:

>100:1 @ 300 - 400nm (Typical)
 >50,000:1 @ 450 - 550nm (Typical)
 >800:1 @ 700 - 1400nm (Typical)
 >1000:1 @ 1400 - 2650nm (Typical)

Substrate:

Fused Silica (Corning 7980)

Wavelength Range (nm):

300 - 2700

Polarization Axis Mark (°):

±2

Threading & Mounting**Mount Thickness (mm):**

4.5

Environmental & Durability Factors**Operating Temperature (°C):**

-50 to 80

Regulatory Compliance**RoHS 2015:**

Compliant

Certificate of Conformance:[View](#)**REACH 241:**

Compliant

Country of Origin:

China

Imported By:

Edmund Optics India Private Limited
 267, Greystone Building, Second Floor,
 6th Cross Rd, Binnamangala,
 Stage 1, Indiranagar, Bengaluru,
 Karnataka, India 560038
 Phone: +91- 80-6845 0000

Product Details

The input beam should enter through the front of the optic, which is the engraved side.

- Wide Acceptance Angles
- Broadband Performance from 300 -2700nm
- Compact Designs Ease System Integration

Broadband Polarizers are ideal solutions for broadband applications from the UV to SMIR where wire grid polarizers are not practical. Broadband Polarizers feature acceptance angles of ±40° and are well suited for use with uncollimated light sources. Additionally, these polarizers utilize a proprietary design that allows for consistent transmitted contrast from 300 – 2700nm.

Note: The input beam should enter through the front of the optic, which is the engraved side.

Technical Information