

[See all 30 Products in Family](#)

25.4mm Dia., 355nm, $\lambda/4$ High Energy Waveplate



High Energy Quartz Waveplates

Stock #39-164 **4 In Stock**

MRP ₹66,084

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹66,084 each
Qty 11+	₹61,543 each
Need More?	Request Quote

Product Downloads

General

High Energy Waveplate **Type:**

Physical & Mechanical Properties

18.0 **Clear Aperture CA (mm):**

25.40 **Diameter (mm):**

Dimensional Tolerance (mm):
+0/-0.2

Construction:
Optically Bonded on UVFS (C7980) Substrate

Parallelism (arcsec):
<3

Optical Properties

Coating:
 $R_{avg} < 0.3\%$

Design Wavelength DWL (nm):
355

Substrate:
Crystalline Quartz

Retardance:
N4

Surface Quality:
20-10

Transmitted Wavefront, P-V:
<N10 @ 632.8nm

Retardance Tolerance:
N150 @ 20°C

Damage Threshold, By Design:
>20 J/cm² @ 1064nm, 10ns, 10Hz

Retardance Order:
2nd

Threading & Mounting

Mount Thickness (mm):
6 ±0.2

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 247:
[Compliant](#)

Country of Origin:
China

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Damage Threshold up to >20 J/cm² @ 1064nm
- N4 and N2 Retardance
- Black Anodized Aluminum Mount
- UV to NIR Design Wavelengths Available

High Energy Quartz Waveplates are available in both N4 and N2 retardance for discrete laser wavelengths from the UV to NIR and can withstand energy densities up to >20 J/cm² at 1064nm. A large acceptance angle and wide operating temperature range enables these waveplates to be integrated into harsh environments applications. High Energy Quartz Waveplates are mounted in a black anodized aluminum housing for easy identification and system integration.