

25.4mm Dia. 405nm $\lambda/4$ Quartz Waveplate Zero Order



Stock #14-297 **4 In Stock**

₹38,769

ADD TO CART

Volume Pricing	
Qty 1-5	₹38,769 each
Qty 6+	₹31,374 each
Need More?	Request Quote

Product Downloads

General

Crystalline Waveplate **Type:**

Air Spaced **Configuration:**

Physical & Mechanical Properties

20.00 **Clear Aperture CA (mm):**

25.40 +0.00/-0.25 **Diameter (mm):**

6.00 +0.00/-0.25	Thickness (mm):
Crystalline	Construction:
<3	Parallelism (arcsec):
Optical Properties	
Laser V-Coat (405nm)	Coating:
405	Design Wavelength DWL (nm):
Crystal Quartz	Substrate: □
$\lambda/4$	Retardance:
10-5	Surface Quality:
$\lambda/10$	Transmitted Wavefront, P-V:
$\pm\lambda/300$	Retardance Tolerance:
0.0001	Temperature Coefficient ($\lambda^\circ\text{C}$):
$R_{\text{abs}} < 0.2\% @ 405\text{nm}$	Coating Specification:
0	Retardance Order:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:
China	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Zero Order and Multiple Order Waveplates
- $\lambda/4$ and $\lambda/2$ Retardance
- Mounted in Black Anodized Aluminum Frame
- [Zero Order Polymer Waveplates](#) Also Available

Quartz Waveplates (Retarders) are available in multiple order and zero order. These waveplates are ideal for a range of applications. Multiple order waveplates are ideal for applications where the wavelength deviates less than $\pm 1\%$ from the design wavelength of the waveplate. For applications with a greater than $\pm 1\%$ deviation, zero order waveplates are recommended due to their increased bandwidth and lower sensitivity to temperature change. Quartz Waveplates (Retarders) have the fast axis marked on the edge of the mount to ease system integration.



Technical Information



