

TECHSPEC[®] 25.4mm Dia. x 2000mm ROC, Uncoated, Convex Laser Mirror



Stock #27-639 1 In Stock

-

1

+

₹10,198

ADD TO CART

Volume Pricing	
Qty 1-5	₹10,198 each
Qty 6-25	₹9,731 each
Qty 26+	₹9,420 each
Need More?	Request Quote

Product Downloads

General	
ConvexMirror	Type:
Physical & Mechanical Properties	
5.96	Center Thickness CT (mm):
5.96	Clear Aperture CA (mm):

25.40 +0.00/-0.12	Diameter (mm):
6.00 ±0.2	Edge Thickness ET (mm):
90	Clear Aperture (%):
Commercial Polish	Back Surface:

Optical Properties

Fused Silica (Corning 7980)	Substrate: ☐
2,000.00	Radius R ₁ (mm):
20-10	Surface Quality:
Uncoated	Coating:
6.00	Effective Focal Length EFL (mm):

Regulatory Compliance

View	Certificate of Conformance:
Vietnam	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- High Precision Fused Silica Mirror Substrates
- Large Selection of Diameters and Focal Lengths
- Custom Coating Options Available

TECHSPEC® Uncoated Convex Laser Mirrors offer high precision 20-10 surface quality ideal for laser beam focusing applications. Featuring fused silica substrates, these convex mirrors are resistant to thermal shock and are available in focal lengths from 25mm to 500mm. TECHSPEC Uncoated Convex Laser Mirrors are ideal for applications in environments with temperature fluctuations. Custom coating options including protected metal coatings and dielectric mirror coatings are available.