

25.4mm Dia., 532nm, $\lambda/2$ High Energy Waveplate



High Energy Quartz Waveplates

Stock **#39-171** 10 TO 12 DAYS

- 1 +

₹65,685.00

ADD TO CART

Qty 1-10
₹65,685.00
Qty 11+
₹61,335.00
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm): 18.0
Coating: R _{avg} <0.2%
Design Wavelength DWL (nm): 532
Diameter (mm):

25.40
Substrate: ☐ Crystalline Quartz
Retardance: $\lambda/2$
Surface Quality: 20-10
Type: High Energy Waveplate
Dimensional Tolerance (mm): +0/-0.2
Construction: Optically Bonded on UVFS (C7980) Substrate
Transmitted Wavefront, P-V: $<\lambda/10$ @ 632.8nm
Parallelism (arcsec): <3
Retardance Tolerance: $\lambda/250$ @ 20°C
Mount Thickness (mm): 6 ± 0.2
Damage Threshold, By Design: ☐ $>20 \text{ J/cm}^2$ @ 1064nm, 10ns, 10Hz
Retardance Order: 0

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
