


[See all 21 Products in Family](#)

25.4mm Dia. x 200mm FL, Uncoated, ISP Optics Germanium (Ge) PCX Lens | GE-PX-25-200

See More by [ISP Optics](#)



Stock **#24-850** **4 In Stock**

-

1

+

₹31,842

ADD TO CART

Volume Pricing	
Qty 1+	₹31,842 each
Need More?	Request Quote

Product Downloads

General

Type:	
Plano-Convex Lens	
Model Number:	
GE-PX-25-200	

Physical & Mechanical Properties

Diameter (mm):	
25.40 +0.00/-0.13	
Centering (arcmin):	
<3	

2.20 ±0.20	Center Thickness CT (mm):
2.00	Edge Thickness ET (mm):
22.86	Clear Aperture CA (mm):
Protective as needed	Bevel:

Optical Properties

200.00 @10.6µm	Effective Focal Length EFL (mm):
Uncoated	Coating:
Germanium (Ge)	Substrate: □
60-40	Surface Quality:
λ/20	Irregularity (P-V) @ 10.6µm:
±2	Focal Length Tolerance (%):
597.16	Radius R ₁ (mm):
7.87	f/#:
0.06	Numerical Aperture NA:
2000 - 14000	Wavelength Range (nm):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:
Latvia	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Ideal for Thermal Imaging Applications
 - Uncoated Transmission from 2 – 16µm
 - Available Uncoated or BBAR Coated for 3 - 12µm
 - Due to material supply chain disruptions with germanium, there may be increased lead times and price changes on our germanium products. For more information, please contact our [customer service team](#).
 - Edmund Optics has limited remaining inventory of this part number and no raw material available to supply more once this is depleted. Please contact our Product Support Engineers to help with an alternate solution for your needs.
- Customer Service can provide you the latest price and availability.

ISP Optics Germanium (Ge) Plano-Convex (PCX) Lenses provide transmission and low absorption through the Long-Wave Infrared (LWIR) spectrum, making them useful for thermal imaging applications. Germanium is chemically inert and insoluble in water with a Knoop Hardness of 780, making it ideal for applications requiring rugged optics. However, Germanium is subject to thermal runaway and should be used at temperatures below 100°C. ISP Optics Germanium (Ge) Plano-Convex (PCX) Lenses are available uncoated with a broad transmission range from 2 – 16µm or with a Broadband Anti-Reflection (BBAR) coating for enhanced transmission in the Mid-Wave Infrared (MMIR) and Long-Wave Infrared (LWIR).

Special Handling

Germanium Optics Handling and Cleaning Guidelines

Germanium optics require special handling and cleaning procedures. Always wear gloves during handling to prevent contamination, and wash hands afterward. Avoid contact between Germanium dust and the eyes, skin, or clothing. When not in use, store optics sealed and covered at temperatures between 20°C and 25°C. Do not expose them to temperatures exceeding 100°C when in use.

Handling Guidelines

- Always wear [gloves](#) to prevent damage from skin oils.
- If Germanium dust is present, take the following precautions:
 - Wear safety glasses to protect eyes.
 - Use a dust mask or face mask to avoid inhalation.
 - Wear [gloves](#) to prevent skin contact.
- Maintain storage temperature between 20°C and 25°C with humidity below 30%.
- Wrap Germanium optics in a [lens cloth](#) or [pouch](#) and seal in a [container](#) when not in use.
- Germanium is brittle and heavy—always place it on soft surfaces and avoid dropping it.

Approved Cleaning Solvents

- Ethanol
- Isopropyl Alcohol
- Methanol
- Reagent-Grade Acetone
- Liquid CO₂
- [Shop Now](#)

