

[See all 37 Products in Family](#)

25.4mm Dia f/8 VIS Coated, Molded Acrylic Aspheric Lens



Molded Acrylic Aspheric Lenses



Stock **#48-186** **20+ In Stock**

1 MRP ₹7,466

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-10	₹7,466 each
Qty 11-49	₹6,155 each
Need More?	Request Quote

Product Downloads

General

Aspheric Lens **Type:**

Physical & Mechanical Properties

25.40 ±0.1 **Diameter (mm):**

23.9	Clear Aperture CA (mm):
4.00 ±0.1	Edge Thickness ET (mm):
4.72	Center Thickness CT (mm):
Protective as needed	Bevel:
99.57	Radius R (mm):

Optical Properties

203.00 @ 632.8nm	Effective Focal Length EFL (mm):
0.06	Numerical Aperture NA:
200.1	Back Focal Length BFL (mm):
PMMA	Substrate: <input type="checkbox"/>
±1	Focal Length Tolerance (%):
632.8	Aspheric Design Wavelength (nm):
BBAR (450-650nm)	Coating:
R _{avg} <0.5% @ 450 - 650nm	Coating Specification:
8	f#:
61.4	Abbe Number (v_d):
1.49	Index of Refraction (n_d):
450 - 650	Wavelength Range (nm):
Infinite	Conjugate Distance:
632.8	Focal Length Specification Wavelength (nm):

Material Properties

70	Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
----	---

Environmental & Durability Factors

80	Operating Temperature (°C):
----	------------------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 242:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Prescription Information Available
- Reduced Spherical Aberration
- Broadband AR Coating Option

Our molded acrylic aspheres are economical solutions for a variety of photonic applications. With available prescription information, these lenses are easily integrated into both benchtop and OEM applications. They are available uncoated and with broadband antireflection coatings. Standard diameter sizes of 0.5" and 1" allow them to be easily mounted using our full line of [lens mounts](#).

Compatible Mounts
