

[See all 37 Products in Family](#)

## 25.4mm Dia. f/0.75 NIR Coated, Molded Acrylic Aspheric Lens



Molded Acrylic Aspheric Lenses



Stock #33-266 **9 In Stock**

- 1 + MRP ₹8,071

ⓘ Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-10	₹8,071 each
Qty 11-49	₹6,659 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Aspheric Lens **Type:**

#### Physical & Mechanical Properties

25.40 ±0.1 **Diameter (mm):**

23.9	<b>Clear Aperture CA (mm):</b>
4	<b>Edge Thickness ET (mm):</b>
12.22	<b>Center Thickness CT (mm):</b>
Protective as needed	<b>Bevel:</b>
49.78	<b>Radius R (mm):</b>

## Optical Properties

19.10 @ 632.8nm	<b>Effective Focal Length EFL (mm):</b>
0.67	<b>Numerical Aperture NA:</b>
12.7	<b>Back Focal Length BFL (mm):</b>
PMMA	<b>Substrate:</b> <input type="checkbox"/>
±1	<b>Focal Length Tolerance (%):</b>
632.8	<b>Aspheric Design Wavelength (nm):</b>
BBAR (700-1100nm)	<b>Coating:</b>
R <sub>avg</sub> < 0.5% @ 700 - 1100nm	<b>Coating Specification:</b>
0.75	<b>f#:</b>
61.4	<b>Abbe Number (v<sub>d</sub>):</b>
1.49	<b>Index of Refraction (n<sub>d</sub>):</b>
700 - 1100	<b>Wavelength Range (nm):</b>
Infinite	<b>Conjugate Distance:</b>
632.8	<b>Focal Length Specification Wavelength (nm):</b>

## Material Properties

70	<b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b>
----	---

## Environmental & Durability Factors

80	<b>Operating Temperature (°C):</b>
----	------------------------------------

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 242:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- Prescription Information Available
- Reduced Spherical Aberration
- Broadband AR Coating Option

Our molded acrylic aspheres are economical solutions for a variety of photonic applications. With available prescription information, these lenses are easily integrated into both benchtop and OEM applications. They are available uncoated and with broadband antireflection coatings. Standard diameter sizes of 0.5" and 1" allow them to be easily mounted using our full line of [lens mounts](#).

## Compatible Mounts

---