


TECHSPEC® 25.4mm Dia. λ /20 ZERODUR® Optical Flat



Stock #43-412-000 20+ In Stock

-

1

+

₹15,570

ADD TO CART

Volume Pricing	
Qty 1-10	₹15,570 each
Qty 11-25	₹14,013 each
Qty 26-49	₹13,312 each
Need More?	Request Quote

Product Downloads

General

Type:
Interferometry Window

Physical & Mechanical Properties

Clear Aperture CA (mm):
22.90

1.00 +0.00/-0.04	Diameter (inches):
25.40 +0.00/-1.00	Diameter (mm):
0.50 ±0.06	Thickness (inches):
12.70 ±1.5	Thickness (mm):
≤3	Parallelism (arcmin):
Protective as needed	Bevel:
Single Surface	Construction:
Fine Ground	Edges:
0.24	Poisson's Ratio:
90.3	Young's Modulus (GPa):
620.00	Knoop Hardness (kg/mm ²):

Optical Properties	
Uncoated	Coating:
Yellow Tint	Color:
ZERODUR®	Substrate: □
1.542	Index of Refraction (n _d):
60-40	Surface Quality:
56.2	Abbe Number (v _d):
λ/20	Surface Flatness (P-V):

Material Properties	
2.53	Density (g/cm ³):
0.1	Coefficient of Thermal Expansion CTE (10 ⁻⁶ /°C):

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 211:
View	Certificate of Conformance:
Germany	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Sizes Ranging from ½" Diameter to 14" Diameter
- Each λ/20 Flat 76.2mm and Larger Includes a Certificate of Calibration
- Available with Standard Metallic Mirror Coatings: [λ/10 and λ/20 Mirrors](#)

TECHSPEC® Single Surface Optical Flats are used as a reference (test plate) against which the flatness of an unknown surface may be compared. Each piece is precision polished by our master opticians and tested on a Zygo interferometer to insure the surface flatness. The secondary surfaces of our single surface flats are pitch polished to window quality for viewing the interference pattern. TECHSPEC Single Surface Optical Flats ship in a durable storage case for permanent protection. λ/20 flats that are 76.2mm or larger also include a certificate of calibration.