

TECHSPEC® 25.4mm Dia. x 50.8mm FL, 3-12µm BBAR Coated, ZnSe Plano-Convex Lens

See More by [Coherent®](#)



TECHSPEC Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses

Stock **#11-425** 10 TO 12 DAYS

[Other Coating Options](#)

- 1 + **₹42,630.00**

ADD TO CART

Qty 1-10
₹42,630.00
Qty 11+
₹38,367.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.10

Effective Focal Length EFL (mm):
50.80 @ 10.6µm

Back Focal Length BFL (mm): 49.51
Coating: BBAR (3000-12000nm)
Coating Specification: R _{avg} ≤3.0% @ 3 - 12μm
Substrate:  Coherent® Infrared ZnSe
Surface Quality: 40-20
Power (P-V) @ 632.8nm: λ
Power (P-V) @ 10.6μm: λ10
Irregularity (P-V) @ 10.6μm: λ20
Centering, ETD (μm): ≤12.7
Center Thickness CT (mm): 3.10 ±0.10
Edge Thickness ET (mm): 1.96
Radius R₁ (mm): 71.26
Clear Aperture CA (mm): 22.86
f#: 2.00
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 3000 - 12000
Bulk Absorption Coefficient (cm⁻¹): <0.0005 @ 10.6μm
Surface Roughness (Angstroms): <50 RMS

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View