

[See all 32 Products in Family](#)

25.4mm Dia. x 101mm FL, Uncoated, ISP Optics Zinc Selenide (ZnSe) Meniscus Lens | ZC-PM-25-100

See More by [ISP Optics](#)



Stock **#24-915**

CLEARANCE

3 In Stock

-

1

+

₹40,050

ADD TO CART

Volume Pricing	
Qty 1+	₹40,050 each
Need More?	Request Quote

Product Downloads

General	
Meniscus Lens	Type:
ZC-PM-25-100	Model Number:
Physical & Mechanical Properties	

25.40 +0.00/-0.13	Diameter (mm):
2.60 ±0.20	Center Thickness CT (mm):
<3	Centering (arcmin):
90	Clear Aperture (%):
22.86	Clear Aperture CA (mm):
2.00	Edge Thickness ET (mm):

Optical Properties	
101.00 @ 10.6µm	Effective Focal Length EFL (mm):
Zinc Selenide (ZnSe), CVD Grade	Substrate: □
3.98	f/#:
0.13	Numerical Aperture NA:
Uncoated	Coating:
600 - 18000	Wavelength Range (nm):
±2	Focal Length Tolerance (%):
250.00	Radius R ₁ (mm):
90.78	Radius R ₂ (mm):
60-40	Surface Quality:
λ/20	Irregularity (P-V) @ 10.6µm:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:
Latvia	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

• Positive or Negative Meniscus Lenses

• CVD Grade Zinc Selenide (ZnSe) Ideal for CO₂ Systems

• Uncoated or BBAR Coated for 8 – 12µm

ISP Optics Zinc Selenide (ZnSe) Meniscus Lenses feature positive and negative meniscus designs that minimize spherical aberration. Positive meniscus lenses enable smaller spot sizes than possible with PCXlenses, making them ideal for use in CO₂ laser applications for precise marking or cutting. Negative meniscus lenses are used to increase the focal length when used with additional lenses, decreasing the numerical aperture of an optical system. ISP Optics Zinc Selenide (ZnSe) Meniscus Lenses are available in standard imperial sizes either uncoated or Broadband Anti-Reflection (BBAR) coated for enhanced transmission from 8 – 12µm.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

