

[See all 3 Products in Family](#)

# 25.4mm Dia. x 12.7mm FL, Uncoated, ISP Optics Silicon (Si) Aspheric Lens | ASPH-SI-25-12

See More by [ISP Optics](#)



Stock #24-881 [CONTACT US](#)

- 1 + MRP ₹57,507

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹57,507 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

ASPH-SI-25-12 **Model Number:**

**Physical & Mechanical Properties**

25.40 +0.00/-0.13 **Diameter (mm):**

<20 **Centering, ETD (µm):**

22.86 **Clear Aperture CA (mm):**

0.99	<b>Edge Thickness ET (mm):</b>
4.00 ±0.20	<b>Center Thickness CT (mm):</b>
Protective as needed	<b>Bevel:</b>
Concave	<b>Shape of Back Surface:</b>
<100 Ra	<b>Surface Roughness (□):</b>

## Optical Properties

12.70	<b>Effective Focal Length EFL (mm):</b>
1.00	<b>Numerical Aperture NA:</b>
10.70	<b>Back Focal Length BFL (mm):</b>
<b>Silicon (Si)</b>	<b>Substrate: □</b>
Uncoated	<b>Coating:</b>
60-40	<b>Surface Quality:</b>
0.50	<b>f#:</b>
1200 - 7000	<b>Wavelength Range (nm):</b>
Infinite	<b>Conjugate Distance:</b>
λ/4	<b>Irregularity (P-V) @ 632.8nm:</b>

## Regulatory Compliance

<a href="#">View</a>	<b>Certificate of Conformance:</b>
Latvia	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details

- Transmission from 1.2 - 7µm
- Diffraction-Limited Performance
- Available Uncoated or HDAR Coated for 3 - 5µm

ISP Optics Silicon (Si) Aspheric Lenses provide diffraction-limited performance for weight-sensitive, Mid-Wave Infrared (MWIR) applications. Available uncoated for applications in the 1.2 - 7µm range or with a high durability anti-reflection (HDAR) coating in the 3 - 5µm range, these lenses are ideal for harsh environment or black body radiation applications. Silicon features a Knoop Hardness of 1150 making it harder and less brittle than Germanium. ISP Optics Silicon (Si) Aspheric Lenses feature a low density of 2.329g/cm<sup>3</sup>, making them lightweight alternatives to Germanium and Zinc Selenide.