

[See all 4 Products in Family](#)

# 25.4mm Dia. x 150mm FL, Uncoated, ISP Optics Calcium Fluoride (CaF<sub>2</sub>) DCX Lens | CF-BX-25-150

See More by [ISP Optics](#)



Calcium Fluoride Double-Convex (DCX) Lenses

Stock **#24-765** CLEARANCE **5 In Stock**

1  MRP ₹30,167

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-9	₹30,167 each
Qty 10+	₹27,140 each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

### General

Double-Convex Lens **Type:**

CF-BX-25-150 **Model Number:**

### Physical & Mechanical Properties

25.40 +0.00/-0.13	<b>Diameter (mm):</b>
<3	<b>Centering (arcmin):</b>
Protective as needed	<b>Bevel:</b>
3.40 ±0.20	<b>Center Thickness CT (mm):</b>
2.00	<b>Edge Thickness ET (mm):</b>
22.86	<b>Clear Aperture CA (mm):</b>

## Optical Properties

150.00 @5µm	<b>Effective Focal Length EFL (mm):</b>
Uncoated	<b>Coating:</b>
<a href="#">Calcium Fluoride (CaF<sub>2</sub>)</a>	<b>Substrate:</b> <input type="checkbox"/>
60-40	<b>Surface Quality:</b>
λ	<b>Irregularity (P-V) @ 632.8nm:</b>
119.12	<b>Radius R<sub>1</sub> (mm):</b>
119.12	<b>Radius R<sub>2</sub> (mm):</b>
5.91	<b>f#:</b>
±2	<b>Focal Length Tolerance (%):</b>
0.08	<b>Numerical Aperture NA:</b>
300 - 8000	<b>Wavelength Range (nm):</b>

## Regulatory Compliance


<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>Reach 240:</b>
Latvia	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Product Details


- Greater than 90% Transmission from 350nm-7µm
- Low Index of Refraction
- High Laser Damage Threshold

ISP Optics Calcium Fluoride Double-Convex (DCX) Lenses are ideal for finite imaging applications requiring high transmission in the infrared wavelength spectrum. Calcium Fluoride features greater than 90% transmission from 350nm to 7µm and a low refractive index, allowing it to be used without an antireflective coating. In addition, its low absorption and high damage threshold makes it a popular choice for use with excimer lasers. ISP Optics Calcium Fluoride Double-Convex (DCX) Lenses offer low solubility and superior hardness compared to other fluoride-based substrates, allowing for use in harsh environments.


## Technical Information



**Calcium Fluoride**



**Uncoated**



## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



**Component Handling Tools**