

TECHSPEC® 25.4mm Dia. x 76.2mm FL, VIS-NIR, Inked, Achromatic Lens



Stock **#49-794-INK** 17 TO 22 D= DAYS
[Other Coating Options](#)

- 1 + **₹11,136.00**

ADD TO CART

Qty 1-5
₹11,136.00
Qty 6+
₹8,918.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.40 ±0.025

Effective Focal Length EFL (mm):
76.20

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 71.14
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 24.40
Centering (arcmin) : <1
Center Thickness CT (mm) : 10.00 ±0.20
Center Thickness CT 1 (mm) : 7.00 ±0.10
Center Thickness CT 2 (mm) : 3.00 ±0.10
Radius R₁ (mm) : 50.85
Radius R₂ (mm) : -40.06
Radius R₃ (mm) : -148.78
Edge Thickness ET (mm) : 7.85
Substrate : ☐ N-SSK6 / SF56
Surface Quality : 40-20
f/# : 3.00
Numerical Aperture NA : 0.17
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 1000

Regulatory Compliance

RoHS 2015 : Compliant
REACH 201 : Compliant
Certificate of Conformance : View