

TECHSPEC[®]

25.4mm Dia. x 25.4mm EFL, Protected Aluminum 90° OAP Mirror with Alignment Through Holes



#11-770

Stock **#11-770** 5 In Stock

-

1

+

₹20,241

ADD TO CART

Volume Pricing	
Qty 1-5	₹20,241 each
Qty 6-25	₹18,217 each
Qty 26-50	₹17,205 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General



Type:

Off-Axis Parabolic Mirror	
Physical & Mechanical Properties	
25.40 +0.00/-0.10	Diameter (mm):
<50 RMS	Surface Roughness (Å):
25.40	Y Offset (mm):
1 x Parallel to Focused Beam 1 x Parallel to Collimated Beam	Through Hole Orientation:
4.1	Through Hole Diameter (mm):
Optical Properties	
25.40	Effective Focal Length EFL (mm):
±1	Focal Length Tolerance (%):
25.40	Radius of Curvature (mm):
Protected Aluminum (400-2000nm)	Coating:
Metal	Coating Type:
R _{avg} >85% @ 400 - 700nm R _{avg} >90% @ 400 - 2000nm	Coating Specification:
90	Off-Set Angle (°):
12.7	Parent Focal Length PFL (mm):
λ/8	Surface Figure, RMS:
400 - 2000	Wavelength Range (nm):
80-50	Surface Quality:
Aluminum 6061-T6	Substrate:
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Through Holes Parallel to Focused and Collimated Beams
 - Range of Metallic Coatings Available
 - <50ÅRMS Surface Roughness
- TECHSPEC® Off-Axis Parabolic (OAP) Mirrors with Alignment Through Holes are designed with two through holes, one that aligns with the focal point of beams focused off the parabolic surface and the second parallel to beams collimated by the surface. The hole placements allow for two beams to hit a target or sample simultaneously, which is a technique used to take pump-probe measurements. These OAPs feature aluminum substrates and are diamond turned with a surface roughness of <50ÅRMS that minimizes scatter. TECHSPEC Off-Axis Parabolic Mirrors with Alignment Through Holes are available coated with protected gold, protected aluminum, or UV enhanced aluminum for integration into applications requiring high reflectance from the ultraviolet (UV) to the infrared (IR).
- Note:** Please [contact us](#) for custom options if your application requires a [standard OAP Mirror](#) with a through hole.

TECHNICAL INFORMATION



CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).