

[See all 19 Products in Family](#)

TECHSPEC® 25.4mm Dia. x 3000mm ROC, Uncoated, Convex Laser Mirror



Stock #27-645 **1 In Stock**

⊖ 1 ⊕ MRP ₹14,630

● Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹14,630 each
Qty 6-25	₹13,923 each
Qty 26+	₹13,519 each
Need More?	Request Quote

Product Downloads

General

ConvexMirror **Type:**

Physical & Mechanical Properties

5.97 **Center Thickness CT (mm):**

5.97 **Clear Aperture CA (mm):**

25.40 +0.00/-0.12 **Diameter (mm):**

6.00 ±0.2 **Edge Thickness ET (mm):**

90 **Clear Aperture (%):**

Commercial Polish **Back Surface:**

Optical Properties

Fused Silica (Coming 7980) **Substrate:**

3,000.00 **Radius R₁ (mm):**

20-10 **Surface Quality:**

Uncoated **Coating:**

6.00 **Effective Focal Length EFL (mm):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Vietnam **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- High Precision Fused Silica Mirror Substrates
- Large Selection of Diameters and Focal Lengths
- Custom Coating Options Available

TECHSPEC® Uncoated Convex Laser Mirrors offer high precision 20-10 surface quality ideal for laser beam focusing applications. Featuring fused silica substrates, these convex mirrors are resistant to thermal shock and are available in focal lengths from 25mm to 500mm. TECHSPEC Uncoated Convex Laser Mirrors are ideal for applications in environments with temperature fluctuations. Custom coating options including protected metal coatings and dielectric mirror coatings are available.