


[See all 4 Products in Family](#)

25.4mm Dia. x 500mm FL, 3-5µm BBAR Coated, ISP Optics Silicon (Si) PCX Lens | HDAR35-SI-PX-25-500

See More by [ISP Optics](#)



Stock #24-897 CLEARANCE **2 In Stock**

⊖ 1 ⊕ MRP ₹24,819

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹24,819 each
Need More?	Request Quote

Product Downloads

General

Plano-Convex Lens **Type:**
HDAR35-SI-PX-25-500 **Model Number:**

Physical & Mechanical Properties

25.40 +0.00/-0.13 **Diameter (mm):**

<3	Centering (arcmin):
2.00 ±0.20	Center Thickness CT (mm):
2.00	Edge Thickness ET (mm):
22.86	Clear Aperture CA (mm):
Protective as needed	Bevel:

Optical Properties

500.00 @4µm	Effective Focal Length EFL (mm):
BBAR (3000-5000nm)	Coating:
R _{avg} <0.5% @ 3 - 5µm R _{abs} <1.5% @ 3 - 5µm	Coating Specification:
Silicon (Si)	Substrate: <input type="checkbox"/>
80-50	Surface Quality:
1λ	Irregularity (P-V) @ 632.8nm:
±2	Focal Length Tolerance (%):
1,213.90	Radius R₁ (mm):
19.69	f#:
0.03	Numerical Aperture NA:
3000 - 5000	Wavelength Range (nm):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:
Latvia	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- High-Durability Anti-Reflection (HDAR) Coated for 3 - 5µm
- Ideal for Weight Sensitive Applications
- Available Focal Lengths from 25.4 – 500mm

ISP Optics Silicon (Si) Plano-Convex (PCX) Lenses feature a High Durability Anti-Reflection (HDAR) coating for increased transmission in the 3 - 5µm range. Silicon features a Knoop Hardness of 1150 making it harder and less brittle than Germanium. In addition, the HDAR coating increases the durability of the substrate, enabling use in harsh environments. ISP Optics Silicon (Si) Plano-Convex (PCX) Lenses also feature a low density of 2.329g/cm³, making them ideal for weight-sensitive IR applications such as Near-Infrared (NIR) imaging and infrared spectroscopy.