

TECHSPEC®

25.4mm Dia. x 50.8mm FL, 8-12μm AR Coated, ZnSe Aspheric Lens

See More by [Coherent®](#)



TECHSPEC Zinc Selenide (ZnSe) Aspheric Lenses

Stock **#39-517** 10 TO 12 DAYS

[Other Coating Options](#)



1



₹90,915.00

ADD TO CART

Qty 1-10
₹90,915.00
Qty 11+
₹81,824.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.10

Effective Focal Length EFL (mm):
50.80

Numerical Aperture NA: 0.25
Back Focal Length BFL (mm): 49.35
Substrate:  Coherent® Infrared ZnSe
Asphere Figure Error, RMS @ 632.8nm: λ/2
Coating: BBAR (8000-12000nm)
Coating Specification: R _{avg} <0.5% @ 8 - 12μm
Centering (arcmin): ≤3
Centering, ETD (μm): ≤12.7
Surface Quality: 40-20
Clear Aperture CA (mm): 22.86
Edge Thickness ET (mm): 2.38
Center Thickness CT (mm): 3.50 ±0.10
f/#: 2
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 8000 - 12000
Conjugate Distance: Infinite
Surface Roughness (Angstroms): <50 RMS
Power (P-V) @ 10.6μm: λ/10
Power (P-V) @ 632.8nm: λ/10

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View