

[See all 133 Products in Family](#)

TECHSPEC[®] 25.4mm Diameter x 750mm FL, 1900-2200nm Coated, IR Ultrafast Thin PCX Lens



Stock **#11-629** 8 In Stock

☐ [Other Coating Options](#)

-

1

+

₹14,636

ADD TO CART

Volume Pricing	
Qty 1-5	₹14,636 each
Qty 6-9	₹12,767 each
Qty 10+	₹11,444 each
Need More?	Request Quote

Product Downloads

General	
Plano-Convex Lens	Type:
Physical & Mechanical Properties	
25.40 +0.00/-0.10	Diameter (mm):
<3	Centering (arcmin):

1.60 ±0.10	Center Thickness CT (mm):
1.37	Edge Thickness ET (mm):
22.86	Clear Aperture CA (mm):
Protective as needed	Bevel:

Optical Properties

750.87 @587.6nm	Effective Focal Length EFL (mm):
749.78	Back Focal Length BFL (mm):
BBAR (1900-2200nm)	Coating:
R _{abs} <0.15% @ 1900 - 2200nm	Coating Specification:

Fused Silica IR Grade	Substrate:
20-10	Surface Quality:

1.5λ	Power (P-V) @ 632.8nm:
λ/8	Irregularity (P-V) @ 632.8nm:

±1	Focal Length Tolerance (%):
344.25	Radius R ₁ (mm):

29.53	f/#:
0.017	Numerical Aperture NA:

1900 - 2200	Wavelength Range (nm):
0	Angle of Incidence (°):

Regulatory Compliance

View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited	Imported By:


Product Details

- Ultra-Thin Center Thickness to Limit GDD
- Low Loss Broadband IBS Anti-Reflection Coating
- Ideal for Ultrafast and Laser Optics Applications
- UV or IR Grade Fused Silica Substrates

TECHSPEC® Ultrafast Thin Plano-Convex Lenses are designed with an ultra-thin center thickness to provide a low group delay dispersion (GDD) for ultrafast laser pulses. TECHSPEC Ultrafast Thin Plano-Convex Lenses are ideal for collecting and focusing light from laser sources and their corresponding harmonics, including Ti:sapphire, Yb:YAG, and Nd:YAG, Holmium, and Thulium lasers. These thin PCX lenses are available in standard sizes with effective focal lengths from 50mm to 2000mm.

IR grade fused silica differs from UV grade fused silica by its reduced amount of OH⁻ ions, resulting in higher transmission throughout the NIR spectrum and reduction of transmission in the UV spectrum.

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Compatible Mounts
