

[See all 2 Products in Family](#)

25.4mm Dia. x -63.5mm FL, Uncoated, ISP Optics Calcium Fluoride (CaF<sub>2</sub>) PCV Lens | CF-PC-25-63

See More by [ISP Optics](#)



Stock #24-782

CLEARANCE

1 In Stock

-

1

+

₹13,950

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | ₹13,950 each                  |
| Qty 10+        | ₹12,555 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

General

Plano-Concave Lens

Type:

CF-PC-25-63

Model Number:

Physical & Mechanical Properties

Diameter (mm):

|                      |                           |
|----------------------|---------------------------|
| 25.40 +0.00/-0.13    |                           |
| Protective as needed | Bevel:                    |
|                      |                           |
| 2.00 ±0.20           | Center Thickness CT (mm): |
|                      |                           |
| <3                   | Centering (arcmin):       |
|                      |                           |
| 22.86                | Clear Aperture CA (mm):   |
|                      |                           |
| 5.40                 | Edge Thickness ET (mm):   |

|                                      |                                     |
|--------------------------------------|-------------------------------------|
| Optical Properties                   |                                     |
| -63.50 @ 5µm                         | Effective Focal Length EFL (mm):    |
|                                      |                                     |
| Calcium Fluoride (CaF <sub>2</sub> ) | Substrate: <input type="checkbox"/> |
|                                      |                                     |
| 2.50                                 | f#:                                 |
|                                      |                                     |
| 0.2                                  | Numerical Aperture NA:              |
|                                      |                                     |
| Uncoated                             | Coating:                            |
|                                      |                                     |
| 300 - 8000                           | Wavelength Range (nm):              |
|                                      |                                     |
| ±2                                   | Focal Length Tolerance (%):         |
|                                      |                                     |
| -25.59                               | Radius R <sub>1</sub> (mm):         |
|                                      |                                     |
| 60-40                                | Surface Quality:                    |
|                                      |                                     |
| λ                                    | Irregularity (P-V) @ 632.8nm:       |

|                                     |                             |
|-------------------------------------|-----------------------------|
| Regulatory Compliance               |                             |
| Compliant                           | RoHS 2015:                  |
|                                     |                             |
| View                                | Certificate of Conformance: |
|                                     |                             |
| Compliant                           | Reach 240:                  |
|                                     |                             |
| Latvia                              | Country of Origin:          |
|                                     |                             |
| Edmund Optics India Private Limited | Imported By:                |

## Product Details

• Low Index of Refraction  
• IR Grade Calcium Fluoride Substrates  
• Standard Imperial Sizes for Easy Benchtop Integration

ISP Optics Calcium Fluoride (CaF<sub>2</sub>) Plano-Concave (PCV) Lenses feature IR grade calcium fluoride substrates, providing high transmission in the visible and infrared spectra. Calcium fluoride has a low index of refraction, enabling these lenses to be used without additional Anti-Reflection (AR) coatings. The PCV design diverges incident collimated beams, making them ideal for light projection and beam expansion applications. ISP Optics Calcium Fluoride (CaF<sub>2</sub>) Plano-Concave (PCV) Lenses are available in standard imperial sizes with focal lengths ranging from -25.4 to -500mm.

## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools