

TECHSPEC[®] 25.4mm Square x 75 FL, 532nm AR Coated, Laser Grade PCX Cylinder Lens



Stock #37-593 10 TO 12 DAYS

-

1

+

₹21,924.00

ADD TO CART

Qty 1-5
₹21,924.00
Qty 6+
₹17,574.00
Volume Pricing
Request Quote

Get Product Downloads



Effective Focal Length EFL (mm):
75.00

Substrate:

Fused Silica

 (Corning 7980)

f/#:
3

Numerical Aperture NA:

0.13
Coating: Laser V-Coat (532nm)
Type: Cylinder Lens, Plano-Convex
Back Focal Length BFL (mm): 72.26
Bevel: Protective bevel as needed
Center Thickness CT (mm): 4.00
Center Thickness Tolerance (mm): ±0.1
Clear Aperture CA (mm): 22.86 x 22.86
Coating Specification: R _{abs} <0.25% @ 532nm
Design Wavelength DWL (nm): 532
Dimensional Tolerance (mm): +0.0/-0.025
Dimensions (mm): 25.4 x 25.4
Edge Thickness ET (mm): 1.57
Focal Length Specification Wavelength (nm): 587.6
Radius R₁ (mm): 34.39
Surface Quality: 20-10
Damage Threshold, By Design: ☐ 10 J/cm ² @ 532nm, 20ns, 20Hz
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Plano Axis Wedge (arcmin): <3
Power Axis Wedge (arcmin): <3
Axial Twist (arcmin): <3

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View