

25.4mm Wire Grid Polarizing Cube



Stock **#89-604** **20+ In Stock**

- 1 + MRP ₹53,472

i Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1-5	₹53,472 each
Qty 6-24	₹43,282 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Physical & Mechanical Properties

>90 **Clear Aperture (%):**

Wire Grid **Construction:**

Dimensions (mm):

25.4 x 25.4 x 25.4 ±0.3

Optical Properties

Beam Deviation (arcmin):

<5

Coating Specification:

$R_{avg} < 0.5\%$ @ 400 - 700nm

Efficiency ($T_p \cdot R_s$):

>62% @ 450nm
>65% @ 550nm & 650nm

Extinction Ratio:

1000:1 @ 450nm
2000:1 @ 550nm
3000:1 @ 650nm

Substrate:

N-BK7

Surface Quality:

40-20

Transmission (%):

$T_p > 72\%$ @ 450nm
 $T_p > 75\%$ @ 550nm
 $T_p > 78\%$ @ 650nm

Transmitted Wavefront Distortion (RMS):

<0.33 λ @ 633nm

Wavelength Range (nm):

400 - 700

Regulatory Compliance

RoHS 2015:

Compliant

Certificate of Conformance:

[View](#)

REACH 241:

Compliant

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91-80-6845 0000


Product Details


- High Contrast Over Large Angles of Incidence
- Low Color Shift at Large Angles
- Ideal for Uncollimated Light Sources

Wire Grid Polarizing Cube Beamsplitters are designed for applications using uncollimated light, such as with a broadband white light source. Wire Grid Polarizing Cube Beamsplitters consist of a wire grid polarizer cemented between two precision high tolerance right angle prisms. An anti-reflection coating has been applied to each face of the beamsplitter to provide less than 0.5% average reflection per surface. Additionally, these beamsplitters maintain their contrast spectrally from 400 – 700nm and over a large cone angle of $\pm 25^\circ$.

Technical Information

Wire Grid Polarizing Cube Transmission of P-Polarization





Wavelength	Incident Cone of Light				
	±5°	±10°	±15°	±20°	±25°
400 - 500nm	2,100:1	2,000:1	1,600:1	1,400:1	1,100:1
500 - 600nm	4,000:1	3,900:1	2,900:1	2,600:1	1,900:1
600 - 700nm	6,000:1	5,500:1	4,200:1	3,800:1	2,500:1