

## TECHSPEC® 25mm 532nm, Laser Line Polarizing Cube Beamsplitter



TECHSPEC Laser Line Polarizing Cube Beamsplitters

Stock #48-574 10 TO 12 DAYS

⊖ 1 ⊕ **₹24,795**

**ADD TO CART**

Qty 1-5

₹24,795

Qty 6+

₹19,401

Volume Pricing

[Request Quote](#)

Get Product Downloads

**Beam Deviation (arcmin):**  
±3

**Bevel:**  
Protective bevel as needed

**Clear Aperture (%):**  
90.00

**Coating Specification:**

R<sub>abs</sub> <0.25% @ 532nm

**Construction:**

Cube

**Design Wavelength DWL (nm):**

532

**Dimensions (mm):**

25.0 x 25.0 x 25.0 ±0.1

**Extinction Ratio:**

1000:1

**P-Polarization Transmission (%):**

>95

**S-Polarization Reflection (%):**

>99.5

**Substrate:** 

[N-BK7](#)

**Surface Quality:**

40-20

**Type:**

Linear Polarizer

**Power (fringes) @ 632.8nm:**

1.25

**Irregularity (fringes) @ 632.8nm:**

0.25

## Regulatory Compliance

**RoHS 2015:**

[Compliant](#)

**Reach 219:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

---