


TECHSPEC®

25.4mm Diameter x 1500mm FL, 1900-2200nm Coated, IR Ultrafast Thin PCX Lens



Stock #11-631 10 TO 12 DAYS

[Other Coating Options](#)



1



₹15,834.00

ADD TO CART

Qty 1-5
₹15,834.00
Qty 6+
₹13,833.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.10

Effective Focal Length EFL (mm):
1,501.75 @587.6nm

Back Focal Length BFL (mm):

1500.65
Coating: BBAR (1900-2200nm)
Coating Specification: R _{abs} <0.15% @ 1900 - 2200nm
Substrate: ☐ Fused Silica IR Grade
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/8
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 1.60 ±0.10
Edge Thickness ET (mm): 1.48
Radius R₁ (mm): 688.50
Clear Aperture CA (mm): 22.86
f/#: 59.06
Numerical Aperture NA: 0.009
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 1900 - 2200
Angle of Incidence (°): 0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View