

TECHSPEC®

25.4mm Diameter x 1500mm FL, 370-550nm Coated, Ultrafast Thin PCX Lens



Stock #11-688 10 TO 12 DAYS

-

1

+

₹11,484.00

ADD TO CART

Qty 1-5
₹11,484.00
Qty 6+
₹10,092.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.10

Effective Focal Length EFL (mm):
1,500.00 @ 587.6nm

Back Focal Length BFL (mm):
1500.54

Coating:

BBAR (370-550nm)
Coating Specification: R _{abs} <0.55% @ 370 - 550nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/8
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 1.60 ±0.10
Edge Thickness ET (mm): 1.48
Radius R₁ (mm): 688.50
Clear Aperture CA (mm): 22.86
f/#: 59.06
Numerical Aperture NA: 0.009
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 370 - 550
Angle of Incidence (°): 0
Damage Threshold, By Design: ☐ 7.5 J/cm ² @ 355nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View