


TECHSPEC®

25mm Dia., 0.40mm Thick, Uncoated, Gorilla Glass® Window



Stock #21-232 **20+ In Stock**

1 MRP ₹3,481

Price inclusive of all taxes

ADD TO CART

Gorilla® Glass Windows



Volume Pricing	
Qty 1-5	₹3,481 each
Qty 6-25	₹2,825 each
Qty 26-99	₹2,523 each
Need More?	Request Quote

Product Downloads

- STEP:step
- PDF Drawing:pdf
- IGES:igs
- eDrawing:eprt
- EO Spec Sheet
- [Download All](#)

General

Type: Protective Window	Chemical Strengthening Cycle (hours): 8
Type of Window: Glass	

Physical & Mechanical Properties

Clear Aperture CA (mm): 22.50	Diameter (mm): 25.00 ±0.25
Thickness (mm): 0.40 ±0.05	Bevel: Protective as needed
Clear Aperture (%): 90.00	Edges: Fine Ground
Poisson's Ratio: 0.22	Young's Modulus (GPa): 70

Optical Properties

Coating: Uncoated	Substrate: Gorilla® Glass
Index of Refraction (n_d): 1.5	Surface Quality: 80-50
Wavelength Range (nm): 350 - 2200	

Material Properties

Density (g/cm³): 2.39	Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.58 (0 to +300°C)
---	--

Regulatory Compliance

RoHS 2015: Compliant	Certificate of Conformance: View
Reach 247: Compliant	
Country of Origin: United States	Imported By: Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91-80-6845 0000

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Chemically Strengthened Drawn Glass
- Highly Resistance to Surface Scratches
- Ideal for Electronic Displays

Gorilla® Glass Windows are chemically strengthened to reduce the propagation of surface flaws. These thin windows feature superior surface quality and excellent scratch resistance. With greater than 90% transmission from 350 - 600nm, these windows are excellent protective covers for electronic displays in consumer and industrial applications. Gorilla® Glass Windows are widely used as protective cover glass for high-end display devices such as laptops, televisions and mobile phones. Due to their durable construction, they are ideal for even the most demanding applications.

Technical Information

Quote Your Size

PLEASE ENTER YOUR
REQUIRED SPECIFICATIONS
HERE:

Type

Substrate

Thickness (mm)

Shape ⓘ

Diameter (mm) ⓘ

Length (mm) ⓘ

0

Width (mm) ⓘ

0

Quantity ⓘ

0

GET PRICING

TYPICAL 4-6 WEEK DELIVERY. DELIVERY DATE TO BE CONFIRMED AT TIME OF ORDER.

OTHER SUBSTRATES, DIMENSIONS AND THICKNESSES OUTSIDE OF THOSE SHOWN HERE ARE ALSO AVAILABLE. IF YOU ARE INTERESTED IN A PRODUCT OUTSIDE OF THE SPECIFICATIONS SHOWN IN THIS TABLE, PLEASE [CONTACT US](#) TO DISCUSS MANUFACTURING FEASIBILITY.

Frequently Purchased Together



#36-427 - Norland Optical Adhesive NOA 68, 1 oz. Application Bottle
₹4,407

Qty



#43-635 - 23.75mm Dia., 1mm Thick, Uncoated, Sapphire Window
₹8,496

Qty



#55-044 - HandPlunger (3cc Barrel), Dispenser Units
₹3,957

Qty
























#55-066 - 1/2" Stainless Steel Tips, 14 Gauge (50 Count)
₹3,957

Qty

Compatible Mounts

	Title	Type	Compare	Stock Number	Price	Buy
	25.0mm Optic Dia., Optic Mount	Fixed		#64-560	₹3,305 Request Quote	CONTACT US <input type="text" value="1"/>
	25.0/25.4mm Optic Dia., Optical Cell Assembly	Fixed		#36-461 CLEARANCE	₹10,190 Request Quote	2 In Stock <input type="text" value="1"/>
	5.0 - 25.0mm Optic Height, Metric Bar-Type Optic Holder	Fixed		#55-529	₹10,291 Request Quote	20+ In Stock <input type="text" value="1"/>
	7.0 - 40.0 Optic Height, English Bar-Type Optic Holder	Fixed		#03-676	₹10,694 Request Quote	2 In Stock <input type="text" value="1"/>
	10.0 - 60.0mm Optic Height, Metric Bar-Type Optic Holder	Fixed		#55-530	₹10,896 Request Quote	CONTACT US <input type="text" value="1"/>
	7.0 - 67.0 Optic Height, English Bar-Type Optic Holder	Fixed		#03-669	₹11,703 Request Quote	6 In Stock <input type="text" value="1"/>

	Title	Type	Compare	Stock Number	Price	Buy
 	8.0 - 118.0 Optic Height, English Bar-Type Optic Holder	Fixed		#03-666	₹12,107 Request Quote	10 In Stock <input type="text" value="1"/> 
 	4.0 - 36.0mm Optic Dia., Self-Centering Jaw Clamp	Fixed		#16-077	₹15,840 Request Quote	6 In Stock <input type="text" value="1"/> 
 	25.0/25.4mm Optic Dia., X-Y Translating Optic Mount	Adjustable - Linear (XY)		#62-956	₹27,846 Request Quote	CONTACT US <input type="text" value="1"/> 
 	5.0 - 100.0mm Optic Dia., Self-Centering Jaw Clamp	Fixed		#16-078	₹41,365 Request Quote	CONTACT US <input type="text" value="1"/> 
 	25.0/25.4mm Optic Dia., Precision Gimbal Mount	Adjustable - Gimbal		#54-999	₹46,511 Request Quote	4 In Stock <input type="text" value="1"/> 
 	25.0/25.4mm Optic Dia., X-Y-Z Translating Optic Mount	Adjustable - Linear (XYZ)		#62-959	₹54,481 Request Quote	6 In Stock <input type="text" value="1"/> 
 	25.0/25.4mm Optic Dia., 5 Axes Optical Mount	Adjustable - Linear (XYZ) & Tip-Tilt		#13-776	₹76,173 Request Quote	2 In Stock <input type="text" value="1"/> 

Check out our full selection of mounts [here](#).

Resources

Media Type

- Application Note
- Technical Tool
- Video
- Glossary
- FAQ

APPLICATION NOTE
Anti-Reflection (AR) Coatings

APPLICATION NOTE
An Introduction to Optical Coatings

TECHNICAL TOOL
Beam Displacement Calculator

APPLICATION NOTE
Understanding Optical Windows

VIDEO
Optical Windows Review

APPLICATION NOTE
Optical Glass

[View More](#)