

[See all 75 Products in Family](#)

**TECHSPEC® 25mm Dia., 0.63 NA, Uncoated, NIR Aspheric Lens**



TECHSPEC® Near-Infrared (NIR) Aspheric Lenses

Stock #13-502 **12 In Stock**

[Other Coating Options](#)

- 1 + MRP ₹26,736

● Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹26,736 each
Qty 6-10	₹24,113 each
Qty 11-25	₹22,499 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Aspheric Lens **Type:**

**Physical & Mechanical Properties**

25.00 +0.00/-0.10 **Diameter (mm):**

<3	<b>Centering (arcmin):</b>
22.5	<b>Clear Aperture CA (mm):</b>
2.30	<b>Edge Thickness ET (mm):</b>
7.60 ±0.10	<b>Center Thickness CT (mm):</b>
Protective as needed	<b>Bevel:</b>
Plano	<b>Shape of Back Surface:</b>

## Optical Properties

20.00 @ 780nm	<b>Effective Focal Length EFL (mm):</b>
0.63	<b>Numerical Aperture NA:</b>
15.73	<b>Back Focal Length BFL (mm):</b>
<a href="#">S-LAH64</a>	<b>Substrate:</b> <input type="checkbox"/>
780	<b>Aspheric Design Wavelength (nm):</b>
1.2λ	<b>Asphere Figure Error, RMS @ 632.8nm:</b>
Uncoated	<b>Coating:</b>
40-20	<b>Surface Quality:</b>
0.80	<b>f/#:</b>
47.37	<b>Abbe Number (v<sub>d</sub>):</b>
1.788	<b>Index of Refraction (n<sub>d</sub>):</b>
375 - 2100	<b>Wavelength Range (nm):</b>
Infinite	<b>Conjugate Distance:</b>
780	<b>Focal Length Specification Wavelength (nm):</b>
50.00	<b>Power (diopters):</b>

## Material Properties

6.1	<b>Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):</b>
-----	---

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">Compliant</a>	<b>Reach 224:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
United States	<b>Country of Origin:</b>
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	<b>Imported By:</b>

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

## Product Details

- Optimized for Applications in the NIR
- Uncoated or AR coated versions available
- Multiple Design Wavelengths Available

TECHSPEC® Near-Infrared (NIR) Aspheric Lenses are optimized to eliminate spherical aberration in the near-infrared. Manufactured from S-LAH64 or N-BK7 substrates and polished through a computer numerical controlled (CNC) process, these aspheric lenses achieve high precision performance across the NIR spectrum. These NIR aspheric lenses include uncoated substrates designed at 780nm with coating options at 350-700nm, 600-1050nm, or 900-1700nm. TECHSPEC® Near-Infrared (NIR) Aspheric Lenses are available with low numerical aperture designs for applications that require beam shape to be maintained as well as high numerical aperture designs for light-gathering applications. For custom designed CNC polished aspheric lenses, please contact us.

## Compatible Mounts

---