

TECHSPEC® 25mm Dia., 0.66 Numerical Aperture NIR Coated, Aspheric Lens



Stock **#49-113** 10 TO 12 DAYS

[Other Coating Options](#)

- 1 +

₹26,100.00

ADD TO CART

Qty 1-5
₹26,100.00
Qty 6+
₹20,880.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
18.75 @ 587.6nm

Numerical Aperture NA:
0.66

Back Focal Length BFL (mm): 12.46
Substrate: L-BAL35
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: BBAR (600-1050nm)
Coating Specification: R _{avg} ≤1.5% @ 600 - 1050nm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 22.5
Edge Thickness ET (mm): 1.63
Center Thickness CT (mm): 10.00 ±0.1
f/#: 0.75
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Power (diopters): 53.33

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant