

[See all 4 Products in Family](#)

**TECHSPEC® 25.4mm NIR II  $\lambda/4$  Fresnel Rhomb Retarder**



Stock **#36-143** **2 In Stock**

⊖ 1 ⊕ ₹29,520

**ADD TO CART**

Volume Pricing	
Qty 1-5	₹29,520 each
Qty 6+	₹27,090 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Fresnel Retarder **Type:**

**Physical & Mechanical Properties**

18.81 x 18.81 **Clear Aperture CA (mm):**

±0.10 **Dimensional Tolerance (mm):**

Protective as needed **Bevel:**

25.40

Width (mm):

## Optical Properties

NIR II (750-1550nm)

Coating:

1064

Design Wavelength DWL (nm):

N-BK7

Substrate:

$\lambda/4$

Retardance:

20-10

Surface Quality:

750 - 1550

Wavelength Range (nm):

25.4

Entrance and Exit Surface (mm):

## Regulatory Compliance

Compliant

RoHS 2015:

View

Certificate of Conformance:

Compliant

Reach 235:

Singapore

Country of Origin:

Edmund Optics India Private Limited

Imported By:

## Product Details

- Broadband Performance with <2% Retardance Variation
- 12.7mm and 25.4mm Options Available
- $\lambda/4$  Retardance

TECHSPEC® Fresnel Rhomb Retarders are available with design wavelengths of 532nm and 1064nm. By utilizing a specific angle, Fresnel rhomb retarders impart a retardance with each internal reflection of the light, totaling  $\lambda/4$ . Each design is paired with either VIS 0° or NIR II coatings to provide efficient transmission across a broad range of wavelengths. These TECHSPEC Fresnel Rhomb Retarders deliver less than 2% retardance variation across the specified wavelength range and are optimized for use in diode and fiber applications.

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).