

TECHSPEC[®] 25.4mm Square x 100 FL, 266nm AR Coated, Laser Grade PCX Cylinder Lens



Stock #37-576 10 TO 12 DAYS

-

1

+

₹21,924.00

ADD TO CART

Qty 1-5
₹21,924.00
Qty 6+
₹17,574.00
Volume Pricing
Request Quote

Get Product Downloads



Effective Focal Length EFL (mm):
100.00

Substrate:

Fused Silica

 (Corning 7980)

f/#:
4

Numerical Aperture NA:

0.08
Coating: Laser V-Coat (266nm)
Type: Cylinder Lens, Plano-Convex
Back Focal Length BFL (mm): 97.39
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.80
Center Thickness Tolerance (mm): ±0.1
Clear Aperture CA (mm): 22.86 x 22.86
Coating Specification: R _{abs} <0.25% @ 266nm
Design Wavelength DWL (nm): 266
Dimensional Tolerance (mm): +0.0/-0.025
Dimensions (mm): 25.4 x 25.4
Edge Thickness ET (mm): 2.01
Focal Length Specification Wavelength (nm): 587.6
Radius R₁ (mm): 45.85
Surface Quality: 20-10
Damage Threshold, By Design: ☐ 3 J/cm² @ 266nm, 20ns, 20Hz
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Plano Axis Wedge (arcmin): <3
Power Axis Wedge (arcmin): <5
Axial Twist (arcmin): <3

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View