

TECHSPEC[®] 25.4mm x -100mm FL, Uncoated Imaging Grade PCV Cylinder Lens



TECHSPEC[®] Beam Shaping PCV Cylinder Lenses

Stock **#34-624** **1 In Stock**

-

1

+

₹7,629

ADD TO CART

Volume Pricing	
Qty 1-5	₹7,629 each
Qty 6-25	₹6,851 each
Qty 26-49	₹6,500 each
Need More?	Request Quote

Product Downloads

General	
Cylinder Lens, Plano-Concave	Type:
Physical & Mechanical Properties	
25.40 +0.0/-0.025	Diameter (mm):
Protective as needed	Bevel:

3.50	Center Thickness CT (mm):
±0.1	Center Thickness Tolerance (mm):
22.86	Clear Aperture CA (mm):
5.03	Edge Thickness ET (mm):

Optical Properties

-100.00	Effective Focal Length EFL (mm):
N-BK7	Substrate: 
4	f/#:
0.13	Numerical Aperture NA:
Uncoated	Coating:
350 - 2200	Wavelength Range (nm):
-102.31	Back Focal Length BFL (mm):
51.68	Radius R ₁ (mm):
40-20	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
<5	Plano Axis Wedge (arcmin):
<5	Power Axis Wedge (arcmin):

Regulatory Compliance

View	Certificate of Conformance:
China	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Beam Shaping Grade Specifications
 - Used with [TECHSPEC® Imaging Grade PCX Cylinder Lenses](#) for Circularizing Beams
 - Negative Focal Length
- TECHSPEC® Imaging Grade PCV Cylinder Lenses are typically used to diverge collimated light in a single axis. These lenses are designed for system integration due to the tightly controlled specifications and generous volume discounts. TECHSPEC Imaging Grade PCV Cylinder Lenses feature tightly controlled wedge and tilt specifications and are ideal for circularizing elliptical beams in combination with our [TECHSPEC Imaging Grade PCX Cylinder Lenses](#).

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
 - High-precision surface quality and flatness
 - Tight tolerances and complex geometries
 - Scalable production—from prototype to volume
- Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).