

[See all 10 Products in Family](#)

255mm, 1030-1080nm + VIS JENar™ F-Theta Scanning Lens

See More by [Jenoptik](#)



Stock #17-025 **4 In Stock**

1 MRP ₹1,92,146

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹1,92,146 each
Need More?	Request Quote

Product Downloads

General

601948 **Model Number:**

JENar F-Theta **Type:**

Note:
+ VIS options provide >85% Transmission from 500-680nm

Protective Window:
#17-697: One Included

Jenoptik

Manufacturer:

Physical & Mechanical Properties

119.8 +0/-0.2 **Maximum Diameter (mm):**

1400 **Weight (g):**

336 **Flange Distance (mm):**

20 **Input Beam Diameter, 1/e² (mm):**

65.3 **Maximum Length (mm):**

Optical Properties

255.00 **Focal Length FL (mm):**

53.2 **Scan Angle (°):**

169 x 169 **Scan Field (mm):**

F-Theta Only: 14.3
With Scanner: 15 **Telecentricity (°):**

291 **Working Distance (mm):**

500 - 680, 1030 - 1080 **Wavelength Range (nm):**

239 **Scan Field Diameter (mm):**

24 **Focus Size Diameter, 1/e² (µm):**

3670 **GDD Specification (fs²):**

Threading & Mounting

M85 x 1 **Mounting Threads:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Lithuania **Country of Origin:**

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000 **Imported By:**

Product Details

- Ideal for High-Precision Material Processing and Laser Scanning Applications
- Large Scan Fields Up to 320mm x 320mm
- Wide Range of Focal Lengths from 108mm - 330mm
- [Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses](#) Also Available

Jenoptik JENar™ F-Theta Scanning Lenses are designed to provide flat field at the image plane of scanning systems and are used in conjunction with [galvanometers](#), [beam expanders](#), and [laser sources](#). These F-Theta lenses feature a wide range of focal lengths and large scan fields. Optimized for common Nd:YAG, Yb:doped, and fiber laser sources, these lenses are available in wavelength ranges of 355nm, 515-540nm, and 1030-1080nm. With their patented stackable mounting technology, these lenses compensate for thermal stresses and improve the stability of the optical components, ensuring high-precision adjustment and position control in OEM systems. Jenoptik JENar™ F-Theta Scanning Lenses are ideal for high-precision laser material processing and laser scanning applications.

[Contact us](#) if your application requires Jenoptik JENar™ F-Theta Scanning Lenses or [Jenoptik JENar™ Silverline™ F-Theta Scanning Lenses](#) not shown on our website.